



SYLVANIA**COMPACT
FLUORESCENT LAMP****MINI-LYNX
PAR 38
23W/ E27 /827****DIMENSIONS (mm)**

Cap Type: E27 - EN60061-1 sheet -7004-21

ELECTRICAL DATA¹

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Lamp rated wattage	(W) :	23W		25.3W
Lamp operating voltage (rms)	(V) :	230-240V		
Lamp current	(mA) :	185 mA		
Power Factor	:		0.55	

OPERATING CONDITIONS:

Cap Rim temperature	(°C) :			80
Lamp Ambient Temperature	(°C) :		-10	50
Operating Position	:	Unrestricted		
Weight	(g) :	365g		

PERFORMANCE SPECIFICATIONS :

Starting time at 25°C	(s) :			1.5
Warm up Time to 60% stabilized light output	(s) :			100
² Switching Cycles (to 50% Failure)	:		10000	

LAMP LIFE³

Average life (IEC Test Cycle)	(h) :	10000
-------------------------------	-------	-------

PHOTOMETRIC DATA:

	colour no.	Luminous Flux nominal value (lm)	CRI (Class)	Colour Temp. (K)	ILCOS Code
Homelight Deluxe	827	1100	1b	2700	PAR-23/27/1b-E27-121/131

Attention:

Lamps comply with EN 60 968 (Safety Requirements) and EN 60 969 (Performance Requirements) and CE Regulations.

¹Measured according to EN 60 969, at 50 Hz, lamp aged 100h.²Switching Cycle ON time 30s; OFF time 150s, at rated Voltage.³Life test according to EN 60 969.**IP 44****Hg**
2.3mg

Issued by : R & D Noida
Date : 17.06.2011
Revision Date :

DATA SHEET

Specification No. : JL0005
Supersedes :
Page : 1 of 1

SYLVANIA