

Distributed by:



www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 419160

CHOOSE **FIT**®-221 FOR:

- General Purpose Protection and Repair
- Identification and Beautifying Substrates
- Insulation from Environment
- Reduced Longitudinal Shrinkage
- Resistance to Water, Fungus, UV Light (black only)
- Use with **XTRA•GUARD**® 1

2 TO 1 SHRINK RATIO



FIT®-221 APPLICATIONS:

- General Purpose Insulation and Repair
- Wire and Cable Harnessing and Bundling
- Cable and Connector Protection
- Wire and Tubing Splicing and Connecting
- **XTRA•GUARD**® 1 Applications
- Automated Cutting Machines (spools)

CHARACTERISTICS

OPERATING TEMPERATURE:

- -55°C to 135°C

SHRINKAGE RATIO:

- Approximately 2 to 1 at 121°C

COLOR DESCRIPTION:

- 4-Foot Lengths:
 3/64 to 2 Inch — Black, White, Clear, Red, Yellow, Blue, Green
 3 and 4 Inch — Black, Clear
- 6-Inch Lengths:
 3/64 to 1 Inch — Black, White, Clear, Red, Yellow, Blue, Green
 1-1/2 to 3 Inch — Black, Clear
- 1/2 or 1 Inch Cut Pieces: Black
- Spools: See Color Availability Chart Next Page

PHYSICAL PROPERTIES:

- Tensile Strength: 1500 psi, (106 kg/cm²)
- Ultimate Elongation: 200%
- Longitudinal Shrinkage: -5%
- Specific Gravity: 1.35
- Secant Modulus: 2.5×10^4 max.
- Flammability: Self-Extinguishing

CHEMICAL PROPERTIES:

- Corrosive Effect: Passes Copper Stability Test
- Fungus Resistance: No Growth

ELECTRICAL PROPERTIES:

- Dielectric Strength: 500V/mil (197 kV/cm)
- Volume Resistivity: 10^{14} ohm-cm

Packaged Assortments

Assorted Sizes of 6" Lengths
 Each Length – Size Identified
 Assorted Colors

Alpha Part No.	Tubing Size Range	Lengths Per Box
FIT-221-MS-1	3/64" – 3/16" (5 Sizes)	6 per Size (30 Lengths)
FIT-221-MS-2	1/4" – 3/4" (4 Sizes)	4 per Size (16 Lengths)

Recommended For Use With
XTRA•GUARD® 1
 Extra-Premium Grade PVC Jacketed
 General Purpose Cables

SPECIFICATIONS

- MIL-DTL-23053/5C, Class 1, 2
- UL Standard 224 (except for Clear)
- CSA Standard 198 (except for Clear)



Underwriters Laboratories Inc.



Canadian Standards Association

Alpha Part No. And Size	Minimum Supplied I.D.		Maximum Recovered I.D.		Nom. Recovered Wall Thickness		4 Ft. Lengths Total Ftg.	Standard Packages Spools		No. Cut Pieces 6 Inch	No. Cut Pieces 1/2" or 1"
	Inches	mm	Inches	mm	Inches	mm		Tot. Ftg.	Tot. Ftg.		
FIT-221-3/64	0.046	1,17	0.023	0,58	0.016	0,41	100	1000		40	1000
FIT-221-1/16	0.063	1,60	0.031	0,78	0.017	0,43	100	1000	100 70	36	1000
FIT-221-3/32	0.093	2,36	0.046	1,17	0.020	0,50	100	500	100 65	32	1000
FIT-221-1/8	0.125	3,18	0.062	1,58	0.020	0,50	100	500	100 60	28	1000
FIT-221-3/16	0.187	4,75	0.093	2,36	0.020	0,50	100	500	100 50	24	1000
FIT-221-1/4	0.250	6,35	0.125	3,18	0.025	0,63	100	250	100 40	20	1000
FIT-221-3/8	0.375	9,53	0.187	4,75	0.025	0,63	100	200	50 35	16	1000
FIT-221-1/2	0.500	12,70	0.250	6,35	0.025	0,63	20	150	50 32	14	--
FIT-221-3/4	0.750	19,10	0.375	9,53	0.030	0,76	20	250	50 24	12	--
FIT-221-1	1.000	25,40	0.500	12,70	0.035	0,88	20	250	50 16	8	--
FIT-221-1-1/2	1.500	38,10	0.750	19,10	0.040	1,02	20	125	-- --	5	--
FIT-221-2	2.000	50,80	1.000	25,40	0.045	1,16	20	125	-- --	3	--
FIT-221-3	3.000	76,20	1.500	38,10	0.050	1,27	8	100	-- --	2	--
FIT-221-4	4.000	101,60	2.000	50,80	0.055	1,40	8	50	-- --	1	--

SPOOL COLOR AVAILABILITY CHART

FIT-221 Tubing Size	Put-Up	Colors
3/64"	1000'	Black, Clear
1/16"	1000'	All Colors*
	100'	Black, Clear
3/32"	70'	All Colors
	500'	All Colors
	100'	Black, Clear
	65'	All Colors
1/8"	500'	All Colors
	100'	Black, Clear
	60'	All Colors
3/16"	500'	All Colors
	100'	Black, Clear
	50'	All Colors
1/4"	250'	All Colors
	100'	Black, Clear
	40'	All Colors

FIT-221 Tubing Size	Put-Up	Colors
3/8"	200'	All Colors
	50'	Black, Clear
	35'	All Colors
1/2"	150'	All Colors
	50'	Black, Clear
	32'	All Colors
3/4"	250'	All Colors
	50'	Black, Clear
	24"	All Colors
1"	250"	All Colors
	50"	Black, Clear
	16"	All Colors
1-1/2"	125'	Black, Clear
2"	125'	Black, Clear
3"	100'	Black, Clear
4"	50'	Black, Clear

*All colors include black, white, clear, red, yellow, blue, green

**SEE PAGE 116
FOR
ECONOMICAL BULK PACKAGES!**

FIT® Preferred Heat Shrink Products

ECONOMICAL **FIT**®-221 BULK PKGS., IRRADIATED POLYOLEFIN

FIT®-221B

MIL-DTL-23053/5C,
CLASS 1, 2
UL STANDARD 224
CSA STANDARD 198

CHOOSE **FIT**®-221B For:

- General Purpose Protection and Repair
- Identification and Beautifying Substrates
- Insulation from Environment
- Reduced Longitudinal Shrinkage
- Resistance to Water, Fungus, UV Light (black only)
- Use with **XTRA**•**GUARD**® 1

FIT®-221B APPLICATIONS:

- General Purpose Insulation and Repair
- Wire and Cable Harnessing and Bundling
- Cable and Connector Protection
- Wire and Tubing Splicing and Connecting
- **XTRA**•**GUARD**® 1 Applications
- Automated Cutting Machines (spools)



CHARACTERISTICS

OPERATING TEMPERATURE:

- -55°C to 135°C

SHRINKAGE RATIO:

- Approximately 2 to 1 at 121°C

COLOR DESCRIPTION:

- All Bulk Packages: Black, Clear

PHYSICAL PROPERTIES:

- Tensile Strength: 1500 psi, (106 kg/cm²)
- Ultimate Elongation: 200%
- Longitudinal Shrinkage: -5%
- Specific Gravity: 1.35
- Secant Modulus: 2.5 x 10⁴ max.
- Flammability: Self-Extinguishing

CHEMICAL PROPERTIES:

- Corrosive Effect: Passes Copper Stability Test
- Fungus Resistance: No Growth

ELECTRICAL PROPERTIES:

- Dielectric Strength: 500V/mil (197 kV/cm)
- Volume Resistivity: 10¹⁴ ohm-cm

SPECIFICATIONS

- MIL-DTL-23053/5C, Class 1, 2
- UL Standard 224 (except for Clear)
- CSA Standard 198 (except for Clear)



Alpha Part No. and Size	Minimum Supplied I.D.		Maximum Rec. I.D.		Nom. Rec. Wall Thickness		NEW BULK PACKAGES			
							SPOOLS		4 FT. LENGTHS	
	Inches	mm	Inches	mm	Inches	mm	Qty. in Box	Total Spool Size	No. of Pcs.	Total Ftg.
FIT-221B-3/64	0.046	1,17	0.023	0,58	0.016	0,41	3x1000	3000	250x4	1000
FIT-221B-1/16	0.063	1,60	0.031	0,78	0.017	0,43	3x1000	3000	250x4	1000
FIT-221B-3/32	0.093	2,36	0.046	1,17	0.020	0,50	3x500	1500	250x4	1000
FIT-221B-1/8	0.125	3,18	0.062	1,58	0.020	0,50	3x500	1500	250x4	1000
FIT-221B-3/16	0.187	4,75	0.093	2,36	0.020	0,50	2x500	1000	250x4	1000
FIT-221B-1/4	0.250	6,35	0.125	3,18	0.025	0,63	2x250	500	250x4	1000
FIT-221B-3/8	0.375	9,53	0.187	4,75	0.025	0,63	2x200	400	250x4	1000
FIT-221B-1/2	0.500	12,70	0.250	6,35	0.025	0,63	2x150	300	200x4	800
FIT-221B-3/4	0.750	19,10	0.375	9,53	0.030	0,76	1x250	250	125x4	500
FIT-221B-1	1.000	25,40	0.500	12,70	0.035	0,88	1x250	250	75x4	300

2 TO 1 SHRINK RATIO

Recommended For Use With
XTRA•**GUARD**® 1
Extra-Premium Grade PVC Jacketed
General Purpose Cables



Toll Free: 1-800-52 ALPHA • Telephone: 908-925-8000 • Fax: 908-925-6923
Europe/UK Telephone: +44 (0) 1932 772422 • Europe/UK Fax: +44 (0) 1932 772433

Web Site: www.alphawire.com
Email: info@alphawire.com