





REV.	DATE	DESCRIPTION
A	02/06/00	UPDATE TITLE/ INSULATOR MATERIAL
B	07/19/07	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex			
8						DRAWN G.R.S.	07/19/07				
7						CHECKED		PART DESCRIPTION TNC R/A CRIMP PLUG (FOR BELDEN RG-8/X TIMES LMR-240MA CABLE)			
6						ISSUED					
5	COVER	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET 1 OF 1		PART NO. 122414			
4	FERRULE	COPPER	NICKEL	1							
3	CONTACT PIN	BRASS	GOLD	1				DWG. NO. 122414.DWG			
2	INSULATOR	TEFLON	NATURAL	1							
1	BODY	BRASS	NICKEL	1				REV. B	SIZE A	SCALE NA	
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/122/122414.DWG					