

[Back](#)
**Selected Cable: 17751**

| End View | Plug                                                                              | Cord                                                                              | Connector                                                                         | End View                                                                            |
|----------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|          |  |  |  |  |
| NONE     | 3"STRIP                                                                           | SVT<br>BELDFOIL<br>SHIELDED                                                       | 910                                                                               | C13                                                                                 |

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| <b>Part Number</b>                | 17751                                        |
| <b>Category</b>                   | 3 conductor plastic original equipment cords |
| <b>Shielding</b>                  | Beldfoil Shielded                            |
| <b>Jacket Color</b>               | black                                        |
| <b>Length Feet</b>                | 6'7"                                         |
| <b>Length Meters</b>              | 2                                            |
| <b>Temperature Rating</b>         | 60 C°C                                       |
| <b>Packaging Units Per Carton</b> | H-100,H-25                                   |
| <b>Color Coding</b>               | International                                |
| <b>AWG Stranding</b>              | 18 (41x34)                                   |
| <b>Nominal OD Inch</b>            | 0.27                                         |
| <b>Nominal OD millimeter</b>      | 6.86                                         |
| <b>Rating</b>                     | 1250 Watts 10A-125V (*)                      |
| <b>Notes</b>                      | (*)Dual rated at 10A-250V.                   |

**Cord View****Approvals**



Qty:

**Back**

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

