




# DUAL-IN-LINE SOCKETS

## SERIES 605, 614 • CARRIER TYPE, LOW PROFILE • OPEN FRAME



- Low profile receptacles sit only .031" high above the board
- Removable plastic carriers can be returned for reloading
- Hi-Rel, 3-finger BeCu #11 contact is rated at 3 amps. See page 251 for details
- Series 605 and 614 use MM #1407 & #0548 pins. See page 157 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



| Total number of pins                                                                               |  |     |     | Quantity per tube | ORDERING INFORMATION                       |                                            |                                                                                     |  |           |           |  |
|----------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----|-----|-------------------|--------------------------------------------|--------------------------------------------|-------------------------------------------------------------------------------------|--|-----------|-----------|--|
|                                                                                                    | A                                                                                 | B   | C   |                   | Length = .146<br>(.039 Min. Mounting Hole) | Length = .155<br>(.035 Min. Mounting Hole) |                                                                                     |  |           |           |  |
| 10                                                                                                 | 0.5                                                                               | 0.2 | 0.3 | 40                | 614-XX-210-31-007000                       | 605-XX-210-11-480000                       | <div><div>RoHS-2<br/>2011/65/EU</div><div>XX=Plating Code<br/>See Below</div></div> |  |           |           |  |
| 4                                                                                                  | 0.2                                                                               | 0.3 | 0.4 | 102               | 614-XX-304-31-007000                       | 605-XX-304-11-480000                       |                                                                                     |  |           |           |  |
| 6                                                                                                  | 0.3                                                                               | 0.3 | 0.4 | 68                | 614-XX-306-31-007000                       | 605-XX-306-11-480000                       |                                                                                     |  |           |           |  |
| 8                                                                                                  | 0.4                                                                               | 0.3 | 0.4 | 50                | 614-XX-308-31-007000                       | 605-XX-308-11-480000                       |                                                                                     |  |           |           |  |
| 10                                                                                                 | 0.5                                                                               | 0.3 | 0.4 | 40                | 614-XX-310-31-007000                       | 605-XX-310-11-480000                       |                                                                                     |  |           |           |  |
| 14                                                                                                 | 0.7                                                                               | 0.3 | 0.4 | 28                | 614-XX-314-31-007000                       | 605-XX-314-11-480000                       |                                                                                     |  |           |           |  |
| 16                                                                                                 | 0.8                                                                               | 0.3 | 0.4 | 25                | 614-XX-316-31-007000                       | 605-XX-316-11-480000                       |                                                                                     |  |           |           |  |
| 18                                                                                                 | 0.9                                                                               | 0.3 | 0.4 | 22                | 614-XX-318-31-007000                       | 605-XX-318-11-480000                       |                                                                                     |  |           |           |  |
| 20                                                                                                 | 1.0                                                                               | 0.3 | 0.4 | 20                | 614-XX-320-31-007000                       | 605-XX-320-11-480000                       |                                                                                     |  |           |           |  |
| 22                                                                                                 | 1.1                                                                               | 0.3 | 0.4 | 18                | 614-XX-322-31-007000                       | 605-XX-322-11-480000                       |                                                                                     |  |           |           |  |
| 24                                                                                                 | 1.2                                                                               | 0.3 | 0.4 | 16                | 614-XX-324-31-007000                       | 605-XX-324-11-480000                       |                                                                                     |  |           |           |  |
| 28                                                                                                 | 1.4                                                                               | 0.3 | 0.4 | 14                | 614-XX-328-31-007000                       | 605-XX-328-11-480000                       |                                                                                     |  |           |           |  |
| 20                                                                                                 | 1.0                                                                               | 0.4 | 0.5 | 20                | 614-XX-420-31-007000                       | 605-XX-420-11-480000                       |                                                                                     |  |           |           |  |
| 22                                                                                                 | 1.1                                                                               | 0.4 | 0.5 | 18                | 614-XX-422-31-007000                       | 605-XX-422-11-480000                       |                                                                                     |  |           |           |  |
| 24                                                                                                 | 1.2                                                                               | 0.4 | 0.5 | 16                | 614-XX-424-31-007000                       | 605-XX-424-11-480000                       |                                                                                     |  |           |           |  |
| 28                                                                                                 | 1.4                                                                               | 0.4 | 0.5 | 14                | 614-XX-428-31-007000                       | 605-XX-428-11-480000                       |                                                                                     |  |           |           |  |
| 32                                                                                                 | 1.6                                                                               | 0.4 | 0.5 | 12                | 614-XX-432-31-007000                       | 605-XX-432-11-480000                       |                                                                                     |  |           |           |  |
| 24                                                                                                 | 1.2                                                                               | 0.6 | 0.7 | 16                | 614-XX-624-31-007000                       | 605-XX-624-11-480000                       |                                                                                     |  |           |           |  |
| 28                                                                                                 | 1.4                                                                               | 0.6 | 0.7 | 14                | 614-XX-628-31-007000                       | 605-XX-628-11-480000                       |                                                                                     |  |           |           |  |
| 32                                                                                                 | 1.6                                                                               | 0.6 | 0.7 | 12                | 614-XX-632-31-007000                       | 605-XX-632-11-480000                       |                                                                                     |  |           |           |  |
| 36                                                                                                 | 1.8                                                                               | 0.6 | 0.7 | 11                | 614-XX-636-31-007000                       | 605-XX-636-11-480000                       |                                                                                     |  |           |           |  |
| 40                                                                                                 | 2.0                                                                               | 0.6 | 0.7 | 10                | 614-XX-640-31-007000                       | 605-XX-640-11-480000                       |                                                                                     |  |           |           |  |
| 42                                                                                                 | 2.1                                                                               | 0.6 | 0.7 | 9                 | 614-XX-642-31-007000                       | 605-XX-642-11-480000                       |                                                                                     |  |           |           |  |
| 48                                                                                                 | 2.4                                                                               | 0.6 | 0.7 | 8                 | 614-XX-648-31-007000                       | 605-XX-648-11-480000                       |                                                                                     |  |           |           |  |
| 50                                                                                                 | 2.5                                                                               | 0.6 | 0.7 | 8                 | 614-XX-650-31-007000                       | 605-XX-650-11-480000                       |                                                                                     |  |           |           |  |
| 52                                                                                                 | 2.6                                                                               | 0.6 | 0.7 | 7                 | 614-XX-652-31-007000                       | 605-XX-652-11-480000                       |                                                                                     |  |           |           |  |
| 50                                                                                                 | 2.5                                                                               | 0.9 | 1.0 | 8                 | 614-XX-950-31-007000                       | 605-XX-950-11-480000                       |                                                                                     |  |           |           |  |
| 52                                                                                                 | 2.6                                                                               | 0.9 | 1.0 | 7                 | 614-XX-952-31-007000                       | 605-XX-952-11-480000                       |                                                                                     |  |           |           |  |
| 64                                                                                                 | 3.2                                                                               | 0.9 | 1.0 | 6                 | 614-XX-964-31-007000                       | 605-XX-964-11-480000                       |                                                                                     |  |           |           |  |
| SPECIFY PLATING CODE XX =                                                                          |                                                                                   |     |     |                   |                                            | 91                                         | 93                                                                                  |  | 41 ◆      | 43 ◆      |  |
| Sleeve (Pin)    |                                                                                   |     |     |                   |                                            | 200 μ" Sn/Pb                               | 200 μ" Sn/Pb                                                                        |  | 200 μ" Sn | 200 μ" Sn |  |
| Contact (Clip)  |                                                                                   |     |     |                   |                                            | 10 μ" Au                                   | 30 μ" Au                                                                            |  | 10 μ" Au  | 30 μ" Au  |  |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mill-Max:

[614-93-964-31-007000](#) [614-93-952-31-007000](#) [614-93-950-31-007000](#) [614-93-652-31-007000](#) [614-93-650-31-007000](#) [614-93-648-31-007000](#) [614-93-642-31-007000](#) [614-93-640-31-007000](#) [614-93-636-31-007000](#) [614-93-632-31-007000](#) [614-93-628-31-007000](#) [614-93-624-31-007000](#) [614-93-432-31-007000](#) [614-93-428-31-007000](#) [614-93-424-31-007000](#) [614-93-422-31-007000](#) [614-93-420-31-007000](#) [614-93-328-31-007000](#) [614-93-324-31-007000](#) [614-93-322-31-007000](#) [614-93-320-31-007000](#) [614-93-318-31-007000](#) [614-93-316-31-007000](#) [614-93-314-31-007000](#) [614-93-310-31-007000](#) [614-93-308-31-007000](#) [614-93-306-31-007000](#) [614-93-304-31-007000](#) [614-93-210-31-007000](#) [605-93-964-11-480000](#) [605-93-952-11-480000](#) [605-93-950-11-480000](#) [605-93-652-11-480000](#) [605-93-650-11-480000](#) [605-93-648-11-480000](#) [605-93-642-11-480000](#) [605-93-640-11-480000](#) [605-93-636-11-480000](#) [605-93-632-11-480000](#) [605-93-628-11-480000](#) [605-93-624-11-480000](#) [605-93-432-11-480000](#) [605-93-428-11-480000](#) [605-93-424-11-480000](#) [605-93-422-11-480000](#) [605-93-420-11-480000](#) [605-93-328-11-480000](#) [605-93-324-11-480000](#) [605-93-322-11-480000](#) [605-93-320-11-480000](#) [605-93-318-11-480000](#) [605-93-316-11-480000](#) [605-93-314-11-480000](#) [605-93-310-11-480000](#) [605-93-306-11-480000](#) [605-93-304-11-480000](#) [605-93-210-11-480000](#) [605-93-308-11-480000](#) [614-43-964-31-007000](#) [614-43-952-31-007000](#) [614-43-950-31-007000](#) [614-43-652-31-007000](#) [614-43-650-31-007000](#) [614-43-648-31-007000](#) [614-43-642-31-007000](#) [614-43-640-31-007000](#) [614-43-636-31-007000](#) [614-43-632-31-007000](#) [614-43-628-31-007000](#) [614-43-624-31-007000](#) [614-43-432-31-007000](#) [614-43-428-31-007000](#) [614-43-424-31-007000](#) [614-43-422-31-007000](#) [614-43-420-31-007000](#) [614-43-328-31-007000](#) [614-43-324-31-007000](#) [614-43-322-31-007000](#) [614-43-320-31-007000](#) [614-43-318-31-007000](#) [614-43-316-31-007000](#) [614-43-314-31-007000](#) [614-43-310-31-007000](#) [614-43-308-31-007000](#) [614-43-306-31-007000](#) [614-43-304-31-007000](#) [614-43-210-31-007000](#) [605-43-964-11-480000](#) [605-43-952-11-480000](#) [605-43-950-11-480000](#) [605-43-652-11-480000](#) [605-43-650-11-480000](#) [605-43-648-11-480000](#) [605-43-642-11-480000](#) [605-43-640-11-480000](#) [605-43-636-11-480000](#) [605-43-632-11-480000](#) [605-43-628-11-480000](#) [605-43-624-11-480000](#) [605-43-432-11-480000](#)