

HRC cartridge fuses



Pack

Cat.Nos



Technical data and dimensions
(p. 80-81)

Cylindrical type gG

Conform to NF C 60-200 - 63-210/211
IEC 60269-1 and 2-1
Veritas approved

			Ventilas approved				
			Rating (Amps)	Voltage ± (Volts)	Rupture capacity (Amps)		
	Without indicator	With indicator	14 x 38 HRC				
10	133 94		0.5	500	100 000		
10	133 01		1				
10	133 02	134 02	2				
10	133 04	134 04	4				
10	133 06	134 06	6				
10	133 08	134 08	8				
10	133 10	134 10	10				
10	133 12	134 12	12				
10	133 16	134 16	16				
10	133 20	134 20	20				
10	133 25	134 25	25				
	Without striker	With striker	14 x 51 HRC				
10	143 02		2	500	100 000		
10	143 04	145 04	4				
10	143 06	145 06	6				
10	143 10	145 10	10				
10	143 16	145 16	16				
10	143 20	145 20	20				
10	143 25	145 25	25				
10	143 32	145 32	32				
10	143 40	145 40	40				
10	143 50 ⁽¹⁾	145 50 ⁽¹⁾	50				
			22 x 58 HRC				
10	153 04		4			500	100 000
10	153 06		6				
10	153 10	155 10	10				
10	153 16	155 16	16				
10	153 20	155 20	20				
10	153 25	155 25	25				
10	153 32	155 32	32				
10	153 40	155 40	40				
10	153 50	155 50	50				
10	153 63	155 63	63				
10	153 80	155 80	80				
10	153 96	155 96	100				
10	153 97 ⁽¹⁾	155 97 ⁽¹⁾	125	400			

(1) Overrating described by standards

HRC cartridge fuses (continued)



Pack

Cat.Nos



Technical data and dimensions
(p. 80-81)

Cylindrical type aM (motor rated)

Conform to NF C 60-200 - EN 60269-1
IEC 60269-1

Veritas approved

			Veritas approved		
	Without striker	With striker	Rating (Amps)	Voltage $\pm$ (Volts)	Rupture capacity (Amps)
8.5 x 31.5					
10	120 01		1	400	20 000
10	120 02		2		
10	120 04		4		
10	120 06		6		
10	120 08		8		
10	120 10		10		
Conform to NF C 63-210/211 IEC 60269-1, 2 and 2-1 Veritas approved					
10 x 38 HRC					
10	130 92		0.25	500	100 000
10	130 95		0.50		
10	130 01		1		
10	130 02		2		
10	130 04		4		
10	130 06		6		
10	130 08		8	400	
10	130 10		10		
10	130 12		12		
10	130 16		16		
10	130 20 ⁽²⁾		20		
10	130 25 ⁽²⁾		25		
14 x 51 HRC					
10	140 02	141 02	2	500	100 000
10	140 04	141 04	4		
10	140 06	141 06	6		
10	140 08	141 08	8		
10	140 10	141 10	10		
10	140 12	141 12	12		
10	140 16	141 16	16	400	
10	140 20	141 20	20		
10	140 25	141 25	25		
10	140 32	141 32	32		
10	140 40	141 40	40		
10	140 45 ⁽¹⁾	141 45 ⁽¹⁾	45		
10	140 50 ⁽¹⁾	141 50 ⁽¹⁾	50	400	
22 x 58 HRC					
10	150 16	151 16	16	500	100 000
10	150 20	151 20	20		
10	150 25	151 25	25		
10	150 32	151 32	32		
10	150 40	151 40	40		
10	150 50	151 50	50		
10	150 63	151 63	63	400	
10	150 80	151 80	80		
10	150 96	151 95	100		
10	150 97	151 97	125		

Neutral links

10	123 00	8.5 x 31.5
10	133 00	10 x 38
10	143 00	14 x 51
10	153 00	22 x 58



(1) Overrating described by standards
(2) Overrating not described by standards