




--	--



7

SPECIFICATIONS

FUNCTION:
1P1T OFF-ON

RATINGS: _____

ANSI/UL 1054 and CAN/CSA
16A 125VAC [UR, cUR]
10A 250VAC [UR, cUR]

1/3HP 125/250VAC

EN 61058-1:2002:
10(4)A 250V~ μ 1E4

10(2)A 250V~ μ 5E4 T85/55 [ENE14


CONTACT RESISTANCE:
Initial: 35mΩ Max. at 50VAC

INSULATION
100MΩ M



10,000
50,000

TEMPERATURE:
Operating: -20°C to 105°C (UR, all)



[ENEC14: 10(2)A 250V~]

10,000 Cycles [ENEC14: 10(4)A 250V~]
50,000 Cycles [ENEC14: 10(2)A 250V~]