



HIRSCHMANN

A BELDEN BRAND

Product information PSW 5-24

Fiber Interfaces:Accessories Fiber Interfaces:Plug-in Power Supplies:PSW 5-24

<http://e-catalog.hirschmann.com/link/57078-57141-57139-24575-38463/en/conf/ustate>

Name	PSW 5-24
	
	plug-in power supply
Delivery informations	
Availability	available
Product description	
Description	plug-in power supply
Type	PSW 5-24
Order No.	943 008-001
Electrical interfaces	
Input voltage	90 to 260 VAC; 47 to 60 Hz
Current consumption	400 mA
Power consumption	-
Output voltage	+5 V
Output current	max. 2.4 A
Ripple voltage	max. 75 mVpp
More Interfaces	
Voltage output	extra-low voltage plug, design M8 acc. IEC 947-5-2
Ambient conditions	
Operating temperature	0 °C to +40 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	5% to 95%
Mechanical construction	
Weight	200 g
EMC interference immunity	
EN 61000-6-2 Immunity for industrial environments	EN 61000-6-2
EMC emitted immunity	
EN 55022	EN 55022 limit class B
Scope of delivery and accessories	
Scope of delivery	device

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.