






PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)



SECTION TERMINAISON CONTACT

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D ₀ ±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PA00
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PA00
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PA00
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PA00

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76» AU

LEAD FREE PART NUMBER



SHELL	A±0.38	B±0.12	C±0.10	D ₀ ±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PA00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PA00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PA00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PA00LF

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76» AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	1992-09-11	ANGULAR				0.X	±0.1	size A3	Scale 2
Eng	PESSON	1992-09-11	LINEAR				0.XX	±0.1		
Chr	NIRMAL GEORGE	2009-11-24	0.XX' ±2°				0.XXX	±0.1	ECN	109-0268
Appr	SUDHIR VARMA	2009-11-24	Product family					D-SUB	Spec ref	-
			MALE CONNECTOR DELTA D STD EUROPE					Rev.		K
title			straight,solder type for PCB 1.6mm					dwg no		C01-8646-0095
catalog no			-					CUSTOMER		sheet 1 of 1

