

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212010001](#)
Status: **Active**
Overview: [mpm_connectors](#)
Description: mPm® DIN Valve Connector, Type A, 2 Pole, Terminal No Tails, Black, Nitrile Gasket with IP67 Screw



Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-121201-001 \(PDF\)](#)
[Packaging Specification PK-121201-001 \(PDF\)](#)
[Test Summary STR-1251 \(PDF\)](#)
[Test Summary TS-121201-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121201](#)
IP Rating IP67
Overview [mpm_connectors](#)
Product Name mPm®
Type Field Attachable Connector

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polypropylene
Material - Contact Brass
Material - Coupling Nut N/A
Material - Plating Mating Silver
Orientation 90° Angle
Poles 2
Temperature Range - Operating -25°C to +75°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16A
Voltage - Maximum 250V AC/DC

Material Info
Old Part Number C28200N0R

Reference - Drawing Numbers
[Packaging Specification](#) PK-121201-001
[Product Specification](#) PS-121201-001
[Sales Drawing](#) SD-121201-002
[Test Summary](#) STR-1251, TS-121201-001

EU RoHS
RoHS Compliant by Exemption
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[121201Series](#)