


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. UL AND CSA LOGOS APPEAR ON ALL PARTS AS SHOWN.
2. 'PANDUIT' STAMPED ON ALL PARTS.
3. IF HEX SIZE IS NOT GIVEN, FLAT HEAD SCREW USED.
4. MATERIAL; COPPER
5. FOR USE WITH COPPER WIRE ONLY.
6. $\triangle$ NEMA HOLE SIZES AND SPACING.
7. ADDITIONAL MULTIPLE WIRE COMBINATIONS FOR CD35-36-Q ARE:
 - A. TWO-#10'S
 - B. TWO-#12'S
 - C. TWO-#14'S
 - D. ONE-#10 WITH ONE-#12
 - E. ONE-#12 WITH ONE-#14
8. THESE PARTS ARE ROHS COMPLIANT.

PART NUMBER	COPPER CONDUCTOR SIZE RANGE	CURRENT RATING (AMPS)	BOLT HOLE SIZE	HEX SIZE	Dimensions in inches						STD. PKG. QTY.	STD. CTN. QTY.
					A	W	G	S	C	T		
CD35-36-QY	#14-#6*	50	3/16'	**	2.13	.38	.22	1.00	.38	.07	25	100
CD70-14-QY	#12-#2	90	1/4'	**	2.26	.50	.25	1.00	.38	.09	25	100
CD125-14-QY	#8-#2/0	125	1/4'	**	2.94	.62	.44	1.00	.44	.13	25	100
CD225-56-QY	#6-#4/0	225	5/16'	5/8'	3.38	1.00	.50	1.00	.63	.13	25	100
CD300-38-3Y	#1-350	300	3/8'	3/4'	4.94	1.00	.94	1.00	1.38	.19	3	12
CD400-38-3Y	#1/0-500	400	3/8'	3/4'	5.62	1.50	.94	1.75	.88	.19	3	12
CD650-12-3Y	600-1000	650	1/2'	1-1/8'	6.88	2.00	1.19	1.75	1.75	.25	3	12

*And combinations

C41666_00

								PANDUIT CORP. TINLEY PARK, ILLINOIS				
								CD SERIES COPPER MECHANICAL LUGS CUSTOMER DRAWING				
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
								(.X) ± (.XXX) ± (.XX) ± ANGLES ±				
								DRAWN BY JHNU	MAT'L:		SCALE NONE	
00	3/06	JHNU	LEM	DRAWING RELEASED - ROHS COMPLIANT	PC00348			DATE 3/06	COPPER		DRAWING NO. C41666	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN #	APP	PM	CHK'D				