

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DW

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A2	ECR-12-012115		26OCT'12	EL	WK

NOTE:





1. MATERIAL:

- 1.1 HOUSING: PA46, WITH 30% GF, UL94 V-0, BLACK COLOR.
 1.2 CONTACTS: PHOSPHOR BRONZE.
 1.3 SHELL: BRASS.


2. FINISH:

- 2.1 CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA,
 1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.
 2.2 SHELL: 0.508um [20u"] MIN. NICKEL PLATED.
 PCB GROUND: TIN PLATED.


3. REFLOW SOLDER CAPABLE TO 260°C PER TEC-109-201, CONDITION B.



RECOMMENDED PCB LAYOUT
 RECOMMENDED PCB THICKNESS: 1.6mm.
 TOLERANCE: ±0.05 (TOP VIEW)



OBSOLETE	TRAY	1.27um[50u"]	1-1734714-4
OBSOLETE		0.76um[30u"]	1-1734714-3
OBSOLETE		0.38um[15u"]	1-1734714-2
OBSOLETE	TUBE	0.15um[6u"]	1-1734714-1
OBSOLETE		1.27um[50u"]	1734714-4
OBSOLETE		0.76um[30u"]	1734714-3
OBSOLETE	PACKAGE	0.38um[15u"]	1734714-2
OBSOLETE		0.15um[6u"]	1734714-1
		MIN.GOLD THICKNESS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. CHIEN 20FEB2008

CHK S. HOU 20FEB2008

APVD W. KODAMA 20FEB2008

PRODUCT SPEC

108-57136

APPLICATION SPEC

—

WEIGHT 22.41 GRAMS

CUSTOMER DRAWING

NAME

TE Connectivity

MODULAR JACK, RJ45, MULTI-PORT,
SHIELDED, THRU-HOLE, PANEL GROUND

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734714

—

SCALE

SHEET

1 OF 2

REV A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-



COPYRIGHT 2011


BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
DWDIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



NOTES:

1. MATERIAL:
TUBE: PVC.
BOX: CORRUGATED FIBER.
2. DIMENSION: SEE DRAWING
3. QUANTITY: SEE TABLE
4. WEIGHT: SEE TABLE

13.40KG	10.08G	9	50	450
GROSS WEIGHT	NET WEIGHT	PCS/TUBE	TUBES/BOX	PCS/BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-		
		CHK	-		
		APVD	-		
DIMENSIONS: mm		PRODUCT SPEC	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	MODULAR JACK, RJ45, MULTI-PORT, SHIELDED, THRU-HOLE, PANEL GROUND		
0 PLC ± -		WEIGHT	SIZE		RESTRICTED TO
1 PLC ± 0.3		A3		CAGE CODE	
2 PLC ± 0.2		00779		DRAWING NO	
3 PLC ± 0.15		C=1734714			
4 PLC ± -		CUSTOMER DRAWING		SCALE	
ANGLES ± 3'				SHEET	2 of 2
MATERIAL				REV	A2
FINISH					