





插頭部件 (Plug Component)			頭部剥皮尺寸 (Dimensions)			線材規格 (Wire Styles)	尾部剥皮尺寸 (Dimensions)			端子規格 (Terminal Style)	
顏色(Color)	零件描述(Component)	Qty.	內剥(Stripped)	分線(Split)	顏色(Color)	SPT-2 18AWGx2C 105°C 黑色(Black) Length : 2438.4±50 (96"±2")	分線(Split)	內剥(Stripped)	顏色(Color)	規格描述(Instruction)	端子編號(Style No.)
35P 黑色 (Black)	ME-101A (1-15P, Polarized)	1	6 ⁺¹ ₋₀	15 ± 2	圓邊 (L) (Smooth)		50.8±5	6.35±3	圓邊 (L) (Smooth)	絕緣依尺寸剝除，留膠於線上(半剝) (Strip and Retain outside Insulated)	
鍍鎳 (Nickel-Plated)	(8.0/6.3) 極性端子97662-1 (Polarized Solid Blades)	2	6 ⁺¹ ₋₀	15 ± 2	毛邊 (N) (Ribbed)		50.8±5	6.35±3	毛邊 (N) (Ribbed)	絕緣依尺寸剝除，留膠於線上(半剝) (Strip and Retain outside Insulated)	



B-C2 扎線圖示 (Tied Loop Hank Detail)

REV	DATE	REVISE CONTENT
A	08/06-2012	The first edition is issued and drawing.
F		

- NOTE:
- Hi-Pot Test : 1500V/1Sec ; <0.5mA.
 - Insulation Resistance Test : DC 500/min>100 meg-ohm.
 - Continuity & Polarization Test : No short circuit, break circuit, displacement.
 - Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
 - Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
 - All material according to Non-toxic standard.(Material must be RoHS compliant.)
 - "FMC" logo maybe present on 1-15P.

線材印字 (Wire Printed)		充實, 油墨印字 (Un-Fillers, Printing Ink)				CnC Tech, LLC Industrial Cable and Connector Technology				
包裝方式 (Packing)			DRAWN <i>Chu8.</i>			CUSTOMER				
Tied Hank	See Hank Detail									
Carton Size	480 x 320 x 180		DATE 08/06-2012			P/N No.		800-1808-2-SPT2-BL-0008F (PCIA-3SF-00008F)		
Pack Number	100pcs/ UL Laster Labels									
Carton Print	See Purchase Order					MATERIAL		PVC	UNIT	mm
TYPE		NEMA 1-15P Polarized Power Supply Cord				Customer Approval				
DRAWNING NO.		098MM956		REV	A					