

[Insulated BNCs](#) | [Test Leads](#) | [Accessories & Probes](#)
[Insulated Test Accessories](#) | [Kits](#) | [Cross Reference](#)



BU-00000-*
 Part # color

* 0 - Black	5 - Green
2 - Red	6 - Blue
4 - Yellow	9 - White

CLIPS & INSULATORS

BU-60TBO Threaded Barrel Alligator Clip - 10 Amp



[Enlarge](#)

- Steel, standard Alligator clip with steel threaded barrel
- Connection to any 8-32 male test prod or screw
- Nose width 0.13"
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-60H Alligator Clip with Insulated Acetate Handle 10 Amp

- Stainless steel body, rivet, and spring
- Jaw opens 5/16" (7.9mm)
- Available in black, red, yellow, green, blue and white
- Nose width 0.13"
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)



[Enlarge](#)

Alligator Clip with Acetate Handle & Screw - 10 Amp BU-60HS-* (Steel) BU-60CHS-* (Solid Copper)

- Available in black, red, yellow, green, blue and white
- Nose width 0.13"
- Federal Spec.: Type TCI-1(red), TCI-2 (Black), W-C-440B (BU-60CHS-*)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-61 Alligator Clip with Gold Plated Beryllium Copper Cage Spring Barrel

- Nickel-plated Steel clip and brass insert
- Cage spring accepts standard (0.080dia.) prod needle
- Nose width 0.13"
- Jaw opens 5/16" (7.9mm) max.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Insulated BNCs](#) | [Test Leads](#) | [Insulated Test Accessories](#)
[Accessories & Probes](#) | [Kits](#) | [Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).