

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0357501210
Status: Contact Molex
Overview: ring_tongue_spade_terminals
Description: Ring Tongue Terminal for 14-18 AWG (0.75~2.08mm²), Stud Size 8 M4, Tin Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35750-0300 \(PDF\)](#)
[Packaging Specification PK-35750-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E134962

General
Product Family Ring and Spade Terminals
Series 35750
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview ring_tongue_spade_terminals
Product Name N/A
Type Ring

Physical
Barrel Type Open
Insulation None
Material - Plating Mating Tin
Packaging Type Reel
Plating min - Mating 1.016µm (40µ")
Plating min - Termination 1.016µm (40µ")
Stud Size 8 (M4)
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 3.20mm (.126") max.
Wire Size AWG 14, 16, 18
Wire Size mm² 0.75 - 2.08

Electrical
Voltage - Maximum 300V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-35750-001
Product Specification PS-35750-0300
Sales Drawing SD-35750-12*0



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
35750Series