


Type

WK 160

165 x 165 x 76 mm



Description

IP 54 junction box according to E DIN IEC 60998-2-5, $U_i=690$ V,
Duroplastic, halogen-free
With IP 54 adapters and M40 sealing plugs
Seal range 17-30 mm, with lead seal set

WK 160 L – empty, grey

WK 160 – 16²,
grey, 5 pole screw terminal 16 mm²

Recommended Accessories:

IP 68 cable gland with lock nut

M20 (seal range 6 - 12 mm)

M40 (seal range 16 - 28 mm)

Order No. Packing Qty

416 912 01 12 / 1


416 412 01 12 / 1

227 420 01 50

227 440 01 5

WK 250

256 x 171 x 106 mm



IP 54 junction box according to E DIN IEC 60998-2-5, $U_i=690$ V,
Duroplastic, halogen-free
With IP 54 adapters and M40 sealing plugs
Seal range 17-30 mm, with lead seal set

WK 250 L – empty, grey

WK 250 – 25²,
grey, 5 pole screw terminal 25 mm²

Recommended Accessories:

IP 68 cable gland with lock nut

M20 (seal range 6 - 12 mm)

M40 (seal range 16 - 28 mm)

425 916 01 6 / 1

425 416 01 6 / 1

227 420 01 50

227 440 01 5

WK Terminals

Junction terminals, $U_i=400$ V / 690 V, for



WK 007	5-pole-2,5 ²	460 525 01	1
WK 040	5-pole-2,5 ² /4 ²	840 004 01	10
WK 060	5-pole-6 ²	460 506 01	1
WK 100	5-pole-10 ²	460 510 01	1
WK 160	5-pole-16 ²	460 516 01	1
WK 250	5-pole-25 ²	460 535 01	1

IP 68 cable glands

IP 68 cable gland with strain relief and locknut



Thread	Thread length	Sealing range			
M16	8,0 mm	4 - 10	mm	227 416 01	75
M20	9,0 mm	6 - 12	mm	227 420 01	50
M20	9,0 mm	7 - 14	mm	227 421 01	30
M25	11,0 mm	7 - 16	mm	227 425 01	25
M32	11,0 mm	11 - 21	mm	227 432 01	10
M40	11,0 mm	16 - 28	mm	227 440 01	5