

Search within category

GO

BUY NOW

DESIGN / INSTALL



PQSFPXB4MBU

40GBASE-CR4 Ethernet high speed twinaxial cable assembly with QSFP+ 40 Gbps hot pluggable modular connectors on each end. 4 meters.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Jacket Material	PVC			
Conductor Gauge (AWG)	28			
Color	Blue			
Overall Length (ft.)	13.12			
Overall Length (m)	4			
Nominal Diameter (In.)	0.28			
Nominal Diameter (mm)	7.1			
Standards Met	Compliant to IEEE 802.3ba and SFF-8436, EEPROM compliant to SFF-8436, Flame retardant IEC 60332-3-24			
Performance Level	40 Gb/s			
Cable Color	Blue			
Length (ft.)	13.12			
Flammability Rating	CL11			
CE Compliant	Yes			
Termination End 1	QSFP+ 40 Gbps Connector			
Termination End 2	QSFP+ 40 Gbps Connector			
Application	Top of Rack (ToR) switch to server, End of Row (EoR)/Middle of Row(MoR) switch to switch, Fibre Channel over Ethernet (FCoE), 10Gig™ and 40Gig™ Ethernet, SAS 6G			
Cable Type	Other			
Nominal Cable Outside Diameter (In.)	0.28			
Part Features	Passive low power assembly, 100% performance tested, low latency performance, robust latching, Advanced connector design with a Variety of lengths			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			