

HEX MALE/FEMALE STANDOFFS

Designers' Choice



MALE/FEMALE .250 HEX THREADED STANDOFFS

CHOICE OF: Brass:ASTM-B16



Plating: Nickel (QQ-N-290)

Aluminum: QQ-Q-225/3

Plating: Clear Iridite (Mil-C-5541)

Stainless Steel: ASTM A581/A582

THREAD SIZE	TL EXTERNAL	A INTERNAL
4-40	3/16 (.187)	1/4 (.250)
6-32	1/4 (.250)	3/8 (.375)
8-32	3/8 (.375)	3/8 (.375)



4-40 THREAD			
LENGTH INCHES "L"	STAINLESS STEEL CAT. NO.	BRASS CAT. NO.	ALUMINUM CAT. NO.
1/4 (.250)***	8712	8713	8714
3/8 (.375)**	2087	7200	8400
1/2 (.500)	2088	1944	8401
5/8 (.625)	2089	1945	8402
3/4 (.750)	2090	1946	8403
7/8 (.875)	2091	7201	8404
1 (1.000)	2092	1947	8405
1-1/8 (1.125)	2093	7202	8406
1-1/4 (1.250)	2094	1948	8407
1-3/8 (1.375)	2095	1949	8408
1-1/2 (1.500)	2096	1950	8409
1-5/8 (1.625)	2097	7203	8410
1-3/4 (1.750)	2098	7205	8411
2 (2.000)	2099	1951	8412

6-32 THREAD			
LENGTH INCHES "L"	STAINLESS STEEL CAT. NO.	BRASS CAT. NO.	ALUMINUM CAT. NO.
1/4 (.250)***	8715	8716	8717
3/8 (.375)**	2119	7210	8413
1/2 (.500)	2120	1952	8414
5/8 (.625)	2121	1953	8415
3/4 (.750)	2122	1954	8416
7/8 (.875)	2123	7211	8417
1 (1.000)	2124	1644	8418
1-1/8 (1.125)	2125	7212	8419
1-1/4 (1.250)	2126	1955	8420
1-3/8 (1.375)	2127	1956	8421
1-1/2 (1.500)	2128	1645	8422
1-5/8 (1.625)	2129	7214	8423
1-3/4 (1.750)	2130	7215	8424
2 (2.000)	2131	1646	8425

8-32 THREAD			
LENGTH INCHES "L"	STAINLESS STEEL CAT. NO.	BRASS CAT. NO.	ALUMINUM CAT. NO.
—	—	—	—
3/8 (.375)**	2149	7220	8426
1/2 (.500)	2150	1957	8427
5/8 (.625)	2151	1958	8428
3/4 (.750)	2152	1959	8429
7/8 (.875)	2153	7221	8430
1 (1.000)	2154	1960	8431
1-1/8 (1.125)	2155	7222	8432
1-1/4 (1.250)	2156	1961	8433
1-3/8 (1.375)	2157	1962	8434
1-1/2 (1.500)	2158	1963	8435
1-5/8 (1.625)	2159	7224	8436
1-3/4 (1.750)	2160	7225	8437
2 (2.000)	2161	1964	8438

** Internal Thread .250 Deep


*** Internal Thread .130/.150 Deep

METRIC MALE/FEMALE

HEX THREADED STANDOFFS (5mm & 5.5mm)

A comprehensive range of precision made metric male/female spacers.

MATERIAL: Brass, Nickel Plate.




5mm HEX*	
CAT. NO.	"L"
4313	10mm
4314	12mm
4315	15mm
4316	18mm
4317	20mm
4318	25mm

5.5mm HEX*	
CAT. NO.	"L"
4319	10mm
4320	12mm
4321	15mm
4322	18mm
4323	20mm
4324	25mm

NYLON MALE/FEMALE .250 HEX


MATERIAL: Nylon 6/6

THREAD SIZE	A
4-40	3/16 (.187)
6-32	1/4 (.250)
8-32	3/8 (.375)



LENGTH INCHES "L"	4-40 THREAD CAT. NO.	6-32 THREAD CAT. NO.	8-32 THREAD CAT. NO.
1/4 (.250)	4800	4814*	4828*
3/8 (.375)	4801	4815	4829**
1/2 (.500)	4802	4816	4830
5/8 (.625)	4803	4817	4831
3/4 (.750)	4804	4818	4832
7/8 (.875)	4805	4819	4833
1 (1.000)	4806	4820	4834
1-1/8 (1.125)	4807	4821	4835
1-1/4 (1.250)	4808	4822	4836
1-3/8 (1.375)	4809	4823	4837
1-1/2 (1.500)	4810	4824	4838
1-5/8 (1.625)	4811	4825	4839
1-3/4 (1.750)	4812	4826	4840
2 (2.000)	4813	4827	4841

* Internal Thread .130/.150 Deep ** Internal Thread .250 Deep



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[4313](#)