

RAD-CON-MCX-MCX-SS

Order No.: 2867607



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867607>

Adapter cable, pigtail 30 cm SMA (m) -> N (m)

Commercial data

GTIN (EAN)	 4 017918 945190
Note	Made-to-order
sales group	H178
Pack	1 pcs.
Customs tariff	85442000
Catalog page information	Page 647 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
07/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Connection 1	Plug connector connection
Type of connection	Typ MCX (male)
Connection 2	Plug connector connection
Type of connection	Typ MCX (male)
Fixed cable length	0.3 m

Cable type	RG 316
Cable, attenuation	1.0 dB/m
Minimum bending radius	25.40 mm
External diameter	2.80 mm
Outer sheath, material	PVC
Connection name	Plug connector connection
Type of connection	Typ MCX (male)
Ambient temperature (operation)	-40 °C ... 75 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;