


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: 34COLOR
HOUSING: MOLDED NYLON 6 OR 6,6. AVAILABLE IN TEN COLORS.
CONTACT TIP: STEEL. BRIGHT NICKEL FINISH.

2. P/N: 9302COLOR
HOUSING: MOLDED NYLON 6,6. AVAILABLE IN TEN COLORS.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.
HARDWARE: STAINLESS STEEL NUT. BRASS EYELET. COPPER, TIN PLATED TERMINAL RING.

3. P/N: W-600/COLOR
18 AWG 65X36 TINNED COPPER INSULATION
PVC 0.144 [3.66] NOMINAL O.D.
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.				
					APPROVALS		DATE		
					DRAWN		R.L.		
					APPROVED BY		10/10		
				MATERIAL SEE NOTE.					
				FINISH SEE NOTE.					
NEXT ASSY		USED ON							
APPLICATION				DO NOT SCALE DRAWING					

E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.			
DESCRIPTION PROBE (34) TO SHRD R/A BAN PLG (9302)			
SIZE	CODE IDENT NO.	DRAWING NO.	REV.
B	08505	63334	
SCALE	1:1		SHEET 1 OF 1