





Copyright FCI.


C

D

- NOTES :
- 1- MATERIALS :
BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0
PIN : COPPER ALLOY
- 2- 7N MIN PIN RETENTION IN EITHER DIRECTION
- 3- RoHS COMPATIBLE PRODUCT SPECIFICATION :
a- PLATING : LF means the product is Lead Free,
2µ MIN matte Tin over 1.27µ Nickel underplating.
b- MANUFACTURING PRODUCT SPECIFICATION :
Housing will withstand exposure to 260°C peak temperature
for 30 secondes in a convection infra-red or vapor phase oven.
c- LABELLING :
Meets packaging specs as per GS-14-920
d- LEGAL STATMENT : See GS-47-0004
- 4- PLANE REFERENCE -A- IS GENERATED BY LONG PINS TAIL ROW
WITH LOWEST AREA OF BODY.
SHORT PINS ROW TO BE FLUSH OR HIGHER 0.1 MAX ABOVE REF -A-.
- 5- MINIMUM QUANTITY IN BLI BOX : 500



SCALE 3:1
VIEW WITH
PICK-UP CAP



RECOMMENDED PAD LAYOUT

spec ref	GS-12-652		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		
ISO 406			
ISO 1101			
surface	linear	0.X	±0.30
		0.XX	±0.13
		0.XXX	±0.05
ISO 1302	angular	0°	±/°



www.fci.com

dr A Parrenin 2014/02/28
eng A Parrenin 2014/03/19
chr D Convercey 2014/03/20
appr Gert Dreesbeke 2014/03/21

projection
mm
product family

title
HEADER UNSHROUDED SMT
DOUBLE ROW R/A

cat. no.

size	A3	scale	4:1
ecn no	ELX-B-17245-1		
rel level	Released		
dwg no	10112690C		
rev	E		
Product - Customer Drw		sheet 1 of 1	