

Quartz Crystal

MHz range

SMD-version

model	KX – 20T
frequency	5,0 MHz
mode	fundamental
operating temperature	-40° ~ + 85°C
frequency tolerance at +25°C	± 50 ppm
temperature tolerance at -40° ~ + 85°C	± 100 ppm
load capacitance C_L	16 pF
series resonance R_1 max.	120 Ohm
aging (first year)	± 5 ppm
shunt capacitance C_0 max.	7,0 pF
drive level in mW	0,1
contents of reel	2000 pcs.
RoHS	since production start
part no.	12.87572

