




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

APPROVED

AD

00

DESCRIPTION

DATE

BY

APPROVED

SEE SHEET 1

-

-

-

800 SERIES MACHINED PREMIUM
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D-LF	5-6437538-4
	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D-LF	9-1437538-5
	W/RAILS						840-AR11D-LF	8-1437538-6
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D-LF	8-1437538-4
	HIGH RETENTION						840-AG34D-LF	8-1437538-3
	HIGH RETENTION						832-AG38D-LF	9-6437533-4
	HIGH RETENTION		.595/.605	.700	1.600	2	832-AG34D-LF	2-6437538-5
	W/RAILS						828-AR12D-LF	6-6437538-9
	W/RAILS		.595/.605	.700	1.400	1	828-AR11D-LF	1-6437538-6
	.180 PC LEAD						828-AG43D-LF	6437538-4
OBSOLETE	HIGH RETENTION						828-AG34D-LF	1-6437538-3
	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-LF	5-6437538-1
	W/RAILS		.595/.605	.700	1.200	1	824-AR11D-LF	9-6437537-9
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D-LF	9-6437537-7
	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D-LF	9-6437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D-LF	9-6437537-5
	HIGH RETENTION						824-AG338D-LF	9-6437537-4
	HIGH RETENTION		.295/.305	.400	1.200	1	824-AG334D-LF	9-6437537-3
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D-LF	7-6437537-3
	HIGH RETENTION						820-AG34D-LF	7-6437537-2
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	.900	1	818-AR44D-LF	4-6437539-9
	W/RAILS						818-AR11D-LF	6-6437537-2
	W/RAILS						816-AR11D-LF	5-6437537-4
	HIGH RETENTION		.295/.305	.400	.800	1	816-AG34D-LF	5-6437537-1
	W/RAILS						814-AR11D-LF	3-6437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG43D-LF	3-6437537-2
	HIGH RETENTION						814-AG34D-LF	3-6437537-1
	W/RAILS		.295/.305	.400	.400	3	808-AR11D-LF	1-6437537-9
	.180 PC LEAD						808-AG43D-LF	6437537-5
	HIGH RETENTION						808-AG34D-LF	6437537-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.	

800 SERIES MACHINED PREMIUM
CONTACT PART NUMBER TABLE

OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D	0-1437538-1
	W/RAILS		.595/.605	.700	1.200	1	824-AR11D	9-1437537-9
	-		.395/.405	.500	1.200	1	824-AG66D	9-1437537-8
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D	9-1437537-7
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG45D	6-1437538-6
	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D	9-1437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D	9-1437537-5
	HIGH RETENTION						824-AG33D	8-1437539-2
	HIGH RETENTION						824-AG338D	9-1437537-4
	HIGH RETENTION						824-AG334D	9-1437537-3
OBSOLETE	-		.295/.305	.400	1.200	1	824-AG32D	9-1437537-2
	-						824-AG31D	8-1437537-9
	-						824-AG30D	8-1437537-7
	-		.395/.405	.500	1.200	1	824-AG14D	8-1437537-6
	-						824-AG12D	8-1437537-5
	-		.595/.605	.700	1.200	1	824-AG11D	8-1437537-2
	-						824-AG10D	8-1437537-1
	-		.295/.305	.400	1.100	1	822-AG11D	7-1437537-8
	-						822-AG10D	7-1437537-7
	W/RAILS						820-AR11D	7-1437537-6
OBSOLETE	.180 PC LEAD						820-AG45D	7-1437537-5
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG44D	7-1437537-4
	.180 PC LEAD						820-AG43D	7-1437537-3
	HIGH RETENTION						820-AG34D	7-1437537-2
	-						820-AG12D	6-1437537-9
	-						820-AG11D	6-1437537-6
	-						820-AG10D	6-1437537-4
	.180 PC LEAD W/RAILS						818-AR44D	4-1437539-9
	W/RAILS						818-AR11D	6-1437537-2
	.180 PC LEAD		.295/.305	.400	.900	1	818-AG44D	6-1437537-1
OBSOLETE	HIGH RETENTION S/B 5-1437537-7						818-AG34D	5-1437538-8
	-						818-AG12D	6-1437537-0
	-						818-AG11D	5-1437537-7
	-						818-AG10D	5-1437537-6
	W/RAILS						816-AR11D	5-1437537-4
	.180 PC LEAD		.295/.305	.400	.800	1	816-AG45D	5-1437537-3
	.180 PC LEAD						816-AG44D	5-1437537-2
	HIGH RETENTION						816-AG34D	5-1437537-1
	HIGH RETENTION						816-AG33D	5-1437537-0
	-						816-AG12D	4-1437537-6
OBSOLETE	-						816-AG11D	4-1437537-0
	-						816-AG10D	3-1437537-7
	.180 PC LEAD, W/RAILS S/B 3-1437537-3						814-AR44D	5-1437533-2
	W/RAILS						814-AR11D	3-1437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG45D	3-1437537-4
	.180 PC LEAD						814-AG44D	3-1437537-3
	.180 PC LEAD						814-AG43D	3-1437537-2
	HIGH RETENTION						814-AG34D	3-1437537-1
	-						814-AG12D	2-1437537-9
	-						814-AG11D	2-1437537-4
OBSOLETE	-						814-AG10D	2-1437537-1
	W/RAILS						808-AR11D	1-1437537-9
	.180 PC LEAD		.295/.305	.400	.400	3	808-AG45D	1-1437537-8
	.180 PC LEAD						808-AG44D	1-1437537-7
	.180 PC LEAD						808-AG43D	1-1437537-5
	HIGH RETENTION						808-AG34D	1-1437537-4
	-						808-AG12D	1-1437537-2
	-						808-AG11D	0-1437537-8
	-						808-AG10D	0-1437537-5
	S/B 6-1437529-8		.295/.305	.400	.300	-	806-AG11D	2-1437533-5
OBSOLETE	SUPERSEDED BY 6-1437529-5						806-AG10D	2-1437533-3
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

WEIGHT -

CUSTOMER DRAWING

SCALE 1:1

SHEET 2 OF 4

REV A3

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

DIP SOCKET, 800 SERIES

00779

1437539-2

AMP 4805 REV 31MAR2000

800 SERIES STAMPED ECONOMY
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	W/RAILS	13	.595/.605	.700	2.400	2	848-AR11D-ES-LF	8-1437540-0
OBSOLETE	W/RAILS	14					840-AR12D-ES-LF	6-6447099-8
OBSOLETE	W/RAILS	15					840-AR11D-ESL-LF	7-1437540-2
OBSOLETE	W/RAILS	13	.595/.605	.700	2.000	2	840-AR11D-ES-LF	7-1437540-1
	.180 PC LEAD	15					840-AG44D-ESL-LF	7-1437540-0
OBSOLETE	W/RAILS	15					832-AR11D-ESL-LF	0-6437540-9
OBSOLETE	W/RAILS	13					832-AR11D-ES-LF	0-6437540-8
	.180 PC LEAD	13	.595/.605	.700	1.600	2	832-AG44D-ES-LF	0-6437540-7
	.180 PC LEAD	14					832-AG43D-ES-LF	0-6437540-6
OBSOLETE	.180 PC LEAD W/RAILS	15					828-AR44D-ESL-LF	9-6437539-8
OBSOLETE	W/RAILS	14					828-AR12D-ES-LF	6-6447099-7
OBSOLETE	W/RAILS	13	.595/.605	.700	1.400	1	828-AR11D-ES-LF	9-6437539-6
	.180 PC LEAD	13					828-AG44D-ES-LF	9-6437539-5
OBSOLETE	.180 PC LEAD W/RAILS	15	.295/.305	.400	1.200	1	824-AR47D-ESL-LF	8-6437533-3
OBSOLETE	W/RAILS	13	.295/.305	.400	1.200	1	824-AR31D-ES-LF	8-6437539-7
OBSOLETE	W/RAILS	14	.595/.605	.700	1.200	1	824-AR12D-ES-LF	6-6447099-6
	.180 PC LEAD	15	.595/.605	.700	1.200	1	824-AG44D-ESL-LF	8-6437539-3
	.180 PC LEAD	13	.295/.305	.400	1.100	1	822-AG44D-ES-LF	6-6437539-5
OBSOLETE	W/RAILS	15	.295/.305	.400	1.000	1	820-AR11D-ESL-LF	5-6437539-8
OBSOLETE	W/RAILS	13					820-AR11D-ES-LF	5-6437539-7
OBSOLETE	W/RAILS	15					816-AR11D-ESL-LF	3-6437539-5
OBSOLETE	W/RAILS	13	.295/.305	.400	.800	1	816-AR11D-ES-LF	3-6437539-4
	.180 PC LEAD	15					816-AG44D-ESL-LF	3-6437539-2
OBSOLETE	W/RAILS	13	.295/.305	.400	.700	1	814-AR11D-ES-LF	2-6437539-2
OBSOLETE	W/RAILS	13					808-AR11D-ES-LF	1-6437539-0
	.180 PC LEAD	14	.295/.305	.400	.400	1	808-AG43D-ES-LF	6437537-6
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY
CONTACT PART NUMBER TABLE

17	OBSOLETE	.180 PC LEAD W/RAILS	9	.295/.305	.400	1.200	1	824-AR47D-ESL	8-1437533-3
SUPERSEDED		.180 PC LEAD W/RAILS S/B 8-1437539-3	9	.595/.605	.700	1.200	1	824-AR44D-ESL	8-1437533-2
	17	W/RAILS	9	.295/.305	.400	1.200	1	824-AR31D-ESL	3-1437540-9
OBSOLETE		W/RAILS	6					824-AR31D-ES	8-1437539-7
OBSOLETE		W/RAILS	7					824-AR12D-ES	6-1447099-6
OBSOLETE		W/RAILS	9	.595/.605	.700	1.200	1	824-AR11D-ESL	8-1437539-6
OBSOLETE		W/RAILS	6					824-AR11D-ES	8-1437539-5
OBSOLETE		-	9	.395/.405	.500	1.200	1	824-AG66D-ESL	8-1437539-4
			5					824-AG65D-ES	0-1571180-1
17	OBSOLETE	.180 PC LEAD	9	.595/.605	.700	1.200	1	824-AG44D-ESL	8-1437539-3
		-	7					824-AG32D-ES	8-1437539-1
		-	9					824-AG31D-ESL	7-1437539-7
		-	6	.295/.305	.400	1.200	1	824-AG31D-ES	7-1437539-6
		-	8					824-AG30D-ESL	7-1437539-4
		-	5					824-AG30D-ES	7-1437539-3
		-	7					824-AG12D-ES	7-1437539-2
		-	9	.595/.605	.700	1.200	1	824-AG11D-ESL	7-1437539-0
		-	6					824-AG11D-ES	6-1437539-9
		-	5					824-AG10D-ES	6-1437539-7
OBSOLETE		.180 PC LEAD	6					822-AG44D-ES	6-1437539-5
		-	7					822-AG12D-ES	6-1437539-4
		-	9	.295/.305	.400	1.100	1	822-AG11D-ESL	6-1437539-3
		-	6					822-AG11D-ES	6-1437539-2
17	OBSOLETE	-	5					822-AG10D-ES	6-1437539-0
SUPERSEDED		.180 PC LEAD W/RAILS S/B 7-1437537-4	9					820-AR44D-ESL	7-1437533-1
17	OBSOLETE	W/RAILS	9					820-AR11D-ESL	5-1437539-8
OBSOLETE		W/RAILS	6	.295/.305	.400	1.000	1	820-AR11D-ES	5-1437539-7
		.180 PC LEAD S/B 7-1437537-4	9					820-AG44D-ES	7-1437533-0
		-	7					820-AG12D-ES	5-1437539-6
		-	9					820-AG11D-ESL	5-1437539-3
		-	6					820-AG11D-ES	5-1437539-2
		-	5					820-AG10D-ES	5-1437539-0
OBSOLETE		.180 PC LEAD W/RAILS S/B 4-1437539-9	9					818-AR44D-ESL	6-1437533-4
OBSOLETE		W/RAILS	9					818-AR11D-ESL	4-1437539-8
OBSOLETE		W/RAILS	6					818-AR11D-ES	4-1437539-7
		.180 PC LEAD S/B 6-1437537-1	9	.295/.305	.400	.900	1	818-AG44D-ESL	6-1437533-3
		-	7					818-AG12D-ES	4-1437539-6
		-	9					818-AG11D-ESL	4-1437539-4
		-	6					818-AG11D-ES	4-1437539-3
		-	5					818-AG10D-ES	4-1437539-1
OBSOLETE		-	9					816-AR11D-ESL	3-1437539-5
OBSOLETE		W/RAILS	6					816-AR11D-ES	3-1437539-4
OBSOLETE		W/RAILS	9					816-AG45D-ES	3-1437539-3
OBSOLETE		.180 PC LEAD	5	.295/.305	.400	.800	1	816-AG44D-ESL	3-1437539-2
OBSOLETE		.180 PC LEAD	9					816-AG12D-ES	3-1437539-1
		-	7					816-AG11D-ESL	2-1437539-9
		-	9					816-AG11D-ES	2-1437539-8
		-	6					816-AG10D-ES	2-1437539-6
		-	5					814-AR44D-ESL	5-1437533-3
OBSOLETE		.180 PC LEAD, W/RAILS S/B 3-1437537-3	9					814-AR11D-ESL	2-1437539-3
		W/RAILS	9					814-AR11D-ES	2-1437539-2
OBSOLETE		W/RAILS	6					814-AR11D-ES	2-1437539-2
OBSOLETE		.180 PC LEAD	5	.295/.305	.400	.700	1	814-AG45D-ES	2-1437539-1
SUPERSEDED		.180 PC LEAD S/B 3-1437537-3	9					814-AG44D-ESL	4-1437540-5
		-	7					814-AG12D-ES	2-1437539-0
		-	9					814-AG11D-ESL	1-1437539-7
		-	6					814-AG11D-ES	1-1437539-6
		-	5					814-AG10D-ES	1-1437539-4
		.180 PC W/RAILS, S/B 1437539-9	9					808-AR44D-ESL	3-1437533-1
OBSOLETE		W/RAILS	9					808-AR11D-ESL	1-1437539-1
		W/RAILS	6					808-AR11D-ES	1-1437539-0
OBSOLETE		.180 PC LEAD	9	.295/.305	.400	.400	1	808-AG44D-ESL	0-1437539-9
OBSOLETE		.180 PC LEAD	7					808-AG43D-ES	1-1437537-6
		-	7					808-AG12D-ES	0-1437539-8
		-	9					808-AG11D-ESL	0-1437539-6
		-	6					808-AG11D-ES	0-1437539-5
		-	5					808-AG10D-ES	0-1437539-2
		S/B 7-1437529-1	7					806-AG12D-ES	2-1437533-8
		S/B 1437535-8	9	.295/.305	.400	.300	1	806-AG11D-ESL	8-1437536-5
		S/B 1437535-7	6					806-AG11D-ES	2-1437533-7
		COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

17	OBSOLETE	-	7					864-AG12D-ES	5-1437538-3
		-	9	.895/.905	1.000	3.200	2	864-AG11D-ESL	5-1437538-0
		-	6					864-AG11D-ES	4-1437538-9
17	OBSOLETE	-	5					864-AG10D-ES	3-1437540-2
OBSOLETE		W/RAILS	9					848-AR11D-ESL	6-1437540-2
17	OBSOLETE	W/RAILS	6					848-AR11D-ES	3-1437540-0
OBSOLETE		-	7	.595/.605	.700	2.400	2	848-AG12D-ES	2-1437540-8
		-	9					848-AG11D-ESL	4-1437538-2
17	OBSOLETE	-	6					848-AG11D-ES	2-1437540-6
		-	5					848-AG10D-ES	2-1437540-5
		-	9	.595/.605	.700	2.100	2	842-AG11D-ESL	2-1437540-4
		-	6					842-AG11D-ES	2-1437540-3
17	OBSOLETE	.180 PC LEAD W/RAILS S/B 2-1437540-0	9					840-AR44D-ESL	0-1437534-7
OBSOLETE		W/RAILS	7					840-AR12D-ES	6-1447099-8
OBSOLETE		W/RAILS	9					840-AR11D-ESL	2-1437540-2
OBSOLETE		W/RAILS	6	.595/.605	.700	2.000	2	840-AR11D-ES	2-1437540-1
		.180 PC LEAD	9					840-AG44D-ESL	2-1437540-0
		-	7					840-AG12D-ES	1-1437540-9
		-	9					840-AG11D-ESL	1-1437540-7
		-	6					840-AG11D-ES	1-1437540-6
		-	5					840-AG10D-ES	1-1437540-4
17	OBSOLETE	-	7	.595/.605	.700	1.800	2	836-AG12D-ES	1-1437540-2
		-	9					836-AG11D-ESL	1-1437540-1
		-	6					836-AG11D-ES	1-1437540-0
OBSOLETE		W/RAILS	9					832-AR11D-ESL	0-1437540-9
OBSOLETE		W/RAILS	6					832-AR11D-ES	0-1437540-8
		.180 PC LEAD S/B 1437540-1	8					832-AG45D-ESL	6-1437538-0
		.180 PC LEAD S/B 1437540-7	9	.595/.605	.700	1.600	2	832-AG44D-ESL	9-1437533-5
17	OBSOLETE	.180 PC LEAD	6					832-AG44D-ES	0-1437540-7
OBSOLETE		.180 PC LEAD	7					832-AG43D-ES	0-1437540-6
		-	7					832-AG12D-ES	0-1437540-5
		-	9					832-AG11D-ESL	0-1437540-3
		-	6					832-AG11D-ES	0-1437540-2
		-	5					832-AG10D-ES	0-1437540-1
17	OBSOLETE	.180 PC LEAD W/RAILS	9					828-AR44D-ESL	9-1437539-8
OBSOLETE		W/RAILS	7					828-AR12D-ES	6-1447099-7
OBSOLETE		W/RAILS	9					828-AR11D-ESL	9-1437539-7
OBSOLETE		W/RAILS	6					828-AR11D-ES	9-1437539-6
17	OBSOLETE	.180 PC LEAD	6	.595/.605	.700	1.400	1	828-AG44D-ES	9-1437539-5
		-	7					828-AG12D-ES	9-1437539-4
		-	9					828-AG11D-ESL	9-1437539-2
		-	6					828-AG11D-ES	9-1437539-1
		-	5					828-AG10D-ES	8-1437539-9
		COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL: -
FINISH: -

DWN: R BROWN
CHK: K WRIGHT
APVD: K WRIGHT
PRODUCT SPEC: -
APPLICATION SPEC: -
WEIGHT: -

06MAY04
06MAY04
06MAY04

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME: -
DIP SOCKET, 800 SERIES

SIZE: A1
CAGE CODE: 00779
DRAWING NO: 1437539-2
RESTRICTED TO: -

CUSTOMER DRAWING
SCALE: 1:1
SHEET: 3 OF 4
REV: A3


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00	—		SEE SHEET 1	—	—	—

1000 SERIES MACHINED PREMIUM
CONTACT, LOW INSERTION FORCE
PART NUMBER TABLE

S/B 4-1437538-8		.895/.905	1.000	3.200	2	1064-AG11D	2-1437529-4
S/B 3-1437540-1		.895/.905	1.000	3.200	2	1064-AG10D	2-1437529-3
S/B 3-1437538-0		.595/.605	.700	2.000	2	1040-AG11D	2-1437529-2
S/B 2-1437538-2		.595/.605	.700	1.600	2	1032-AG11D	2-1437529-1
S/B 1437538-4		.595/.605	.700	1.400	1	1028-AG11D	1-1437529-9
S/B 8-1437537-9		.295/.305	.400	1.200	1	1024-AG31D	1-1437529-8
S/B 8-1437537-2		.595/.605	.700	1.200	1	1024-AG11D	1-1437529-6
S/B 8-1437537-1		.595/.605	.700	1.200	1	1024-AG10D	1-1437529-5
S/B 6-1437537-6		.295/.305	.400	1.000	1	1020-AG11D	1-1437529-4
S/B 6-1437537-4						1020-AG10D	1-1437529-3
S/B 5-1437537-7		.295/.305	.400	.900	1	1018-AG11D	1-1437529-2
S/B 5-1437537-6						1018-AG10D	1-1437529-1
S/B 4-1437537-0		.295/.305	.400	.800	1	1016-AG11D	1-1437529-0
S/B 3-1437537-7						1016-AG10D	0-1437529-9
S/B 2-1437537-4		.295/.305	.400	.700	1	1014-AG11D	0-1437529-7
S/B 2-1437537-1						1014-AG10D	0-1437529-6
S/B 1437537-8		.295/.305	.400	.400	3	1008-AG11D	0-1437529-5
S/B 1437537-5						1008-AG10D	0-1437529-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

1800 SERIES MACHINED PREMIUM
CONTACT, LOW GOLD
PART NUMBER TABLE

	S/B 5-1437538-0		.895/.905	1.000	3.200	2	1864-AG111D	5-1437529-1
	S/B 6-1437540-2 W/RAILS		.595/.605	.700	2.400	2	1848-AR111D	5-1437529-0
	S/B 4-1437538-2						1848-AG111D	4-1437529-9
	S/B 2-1437540-4		.595/.605	.700	2.100	2	1842-AG111D	4-1437529-8
	S/B 2-1437540-2 W/RAILS		.595/.605	.700	2.000	2	1840-AR111D	4-1437529-7
	S/B 1-1437540-7						1840-AG111D	4-1437529-6
	S/B 1437540-3		.595/.605	.700	1.600	2	1832-AG111D	4-1437529-5
	S/B 9-1437539-7 W/RAILS		.595/.605	.700	1.400	1	1828-AR111D	4-1437529-4
	S/B 9-1437539-2						1828-AG111D	4-1437529-3
	S/B 3-1437540-9 W/RAILS		.295/.305	.400	1.200	1	1824-AR131D	4-1437529-2
OBSOLETE	S/B 8-1437539-6 W/RAILS		.595/.605	.700	1.200	1	1824-AR111D	4-1437529-1
OBSOLETE	S/B 8-1437539-4		.395/.405	.500	1.200	1	1824-AG141D	4-1437529-0
	S/B 7-1437539-7		.295/.305	.400	1.200	1	1824-AG131D	3-1437529-9
	S/B 7-1437539-0		.595/.605	.700	1.200	1	1824-AG111D	3-1437529-8
	S/B 6-1437539-3		.395/.405	.500	1.100	1	1822-AG111D	3-1437529-7
	S/B 5-1437539-8 W/RAILS		.295/.305	.400	1.000	1	1820-AR111D	3-1437529-6
SUPERSEDED	S/B 5-1437539-3						1820-AG111D	3-1437529-5
	S/B 4-1437539-8 W/RAILS		.295/.305	.400	.900	1	1818-AR111D	3-1437529-4
	S/B 4-1437539-4						1818-AG111D	3-1437529-3
OBSOLETE	S/B 3-1437539-5 W/RAILS		.295/.305	.400	.800	1	1816-AR111D	3-1437529-2
	S/B 2-1437539-9						1816-AG111D	3-1437529-1
	S/B 2-1437539-3 W/RAILS		.295/.305	.400	.700	1	1814-AR111D	3-1437529-0
	S/B 1-1437539-7						1814-AG111D	2-1437529-9
	S/B 1-1437539-1 W/RAILS		.295/.305	.400	.400	3	1808-AR111D	2-1437529-6
	S/B 1437539-6						1808-AG111D	2-1437529-5
OBSOLETE	S/B 1437539-8		.295/.305	.400	.300		1806-AG111D	2-1437529-4
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN CHK K WRIGHT	06MAY04 06MAY04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K WRIGHT	06MAY04	NAME	
	0 PLC ± -	PRODUCT SPEC		DIP SOCKET, 800 SERIES	
	1 PLC ± -	APPLICATION SPEC			
MATERIAL -	FINISH -	WEIGHT -		SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING				DRAWING NO 1437539-2	RESTRICTED TO -
SCALE 1:1				SHEET 4 OF 4	REV A3