

Flexo Wrap

- **Heavy Duty Hook and Loop Closure for Frequent Access**
- **Expands to Fit Over Inline Connectors and Splices**
- **Halogen Free**
- **Temperature Range -94°F to 257°F**
- **Melt Temp. 482°F**

Flexible Control & Management with Easy On, Easy Off Access

FLEXO WRAP (FW) is an exclusive product engineered and manufactured by Techflex. FW provides the perfect solution to a wide variety of unique application challenges.


The color matched hook and loop closure provides for easy on and off installation, as well as instant and convenient access for harness break-outs and rework of any specific section along the entire length of the run. Combined with the expandable, open weave design, FW will conform to a wide variety of bundle diameters and will wrap around irregular shapes.

All grades of FW cut cleanly with a hot knife.

FLEXO WRAP is designed for quick and easy management of wire, cable and hose assemblies. Just separate the hook and loop fasteners along the edge of the material....

and slip the entire length of FW around or under your harness or component assembly. The wide expandability range allows FW to easily fit around...

odd-shaped connectors and gently constrict around the diameter of your wires. When the FW is in place, simply seal the hook and loop along the edges.



Nominal Size	Part #	Hook & Loop Width	Standard Spool Put-Ups		Available Colors	Lbs/ 100'
			Bulk Spool	Shop Spool		
1/2"	FWN0.50	1/4"	100'	20'	BK, WH, GY & BE	1.30
3/4"	FWN0.75	5/8"	100'	15'	BK, WH, GY & BE	1.80
1 1/4"	FWN1.25	5/8"	100'	12'	BK, WH, GY & BE	2.30
2"	FWN2.00	5/8"	100'	10'	BK, WH, GY & BE	3.20
2 1/2"	FXN2.50BK	5/8"	100'	10'	BK	3.75

