


Pluggable Terminal Strips Plug in

Features

- Moulded from PA6
- White colour
- Easily cut to size
- Self extinguishing
- CE Approved
- Glow white test (EN60695) 960°C

Notes: Higher temperature and VO types available on request.

Available pre-cut to length for volume orders.



Specification

Voltage (max)	450Vac
Working temperature	85 °C
No. of poles	12
Moulding	UL94-V2 Self-extinguishing PA 6
Conducting bush	Nickel Plated Brass
Screws	Plated Steel

Type No.	Max Section rigid	Max Section Flexible	Length	Width	Height	Fixing Holes	Insert diameter	Fixing hole pitch	Max Current
CTSN431/12M	2.5mm ²	2.5mm ²	94mm	16mm	15.5mm	2.75mm	2.9mm	8.0mm	17.5A
CTSN431/12F	2.5mm ²	2.5mm ²	94mm	16mm	15.5mm	2.75mm	2.9mm	8.0mm	17.5A
CTSN433/12M	6mm ²	4mm ²	119.4mm	20.5mm	16.4mm	3.2mm	3.4mm	10.25mm	24A
CTSN433/12F	6mm ²	4mm ²	119.4mm	20.5mm	16.4mm	3.2mm	3.4mm	10.25mm	24A
CTSN434/12M	10mm ²	6mm ²	143mm	23.5mm	19mm	3.5mm	4.3mm	12.3mm	57A
CTSN434/12F	10mm ² A	6mm ²	143mm	23.5mm	19mm	3.5mm	4.3mm	12.3mm	57A

Tel: +44 (0)1727 864437 Fax: +44 (0)1727 855400
E-mail: camdeninfo@camdenelec.com Website: www.camdenelec.com

Because we operate a constant improvement policy, our products are subject to change without notice.

CAMDEN
E L E C T R O N I C S L T D