




PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FRHC6**2 (SEE NOTE 1)	78.74 IN $\pm$.18 IN (2000.0mm $\pm$ 4.6mm)	3.54 LB (1606g)	0.54 LB/FT (8.0g/cm)
FRHC6**6 (SEE NOTE 1)	72.00 IN $\pm$.18 IN (1828.8mm $\pm$ 4.6mm)	3.24 LB (1470g)	0.54 LB/FT (8.0g/cm)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37185CD_DC_FRHC6_01.prt

CAD FILENAME/LAYERS



FRHC6.pdf

PANDUIT

CORP

TINLEY PARK, ILLINOIS

FIBERRUNNER 6x4 SNAP-ON HINGED
COVER (FRHC6**2, FRHC6**6)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) $\pm$ (.XXX) $\pm$
(.XX) $\pm$.03 (0.8) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MAT'L:

SCALE

JHNU

PVC

NONE

DATE

DRAWING NO.

DWG

5-11-00

37185-83

A

CHK'D

NEY

SIZE

-	-----	---	---	K. REVISED ENTIRE CHART J. REVISED CAD FILENAME	-----	---	---		
5	7-21-06	DTP	RN	I. REVISED DRAWING TITLE H. REVISED AND REDRAWN	37185-83	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP