


DC-B 6-HM-M

Order No.: 1602164



DUPLICON, aluminum basic housing with enclosed bottom, type B6,
IP67 protection

Commercial data

EAN	 4 046356 027861
Pack	10
Customs tariff	85369010
Country of Origin	SI
Catalog page information	Page 489 (PC-2011)

Product notes

WEEE/RoHS-compliant since:
05/07/2004



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Design	DC-B6
Color	pearl gray
Degree of protection for housing	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	EMC-conductive

Certificates



Certification

VDE-PZI

Accessories


Item Designation Description

General

1602313	DC-B 6-A-SA	DUPLICON, mounting bracket, made of 3 mm high-grade steel plate, with predrilled holes
1602410	T20-M4X12	M4 Torx head screw T20, 12 mm long, self tapping, consisting of high-strength steel, anti-corrosive

Drawings

Dimensioned drawing



Dimensional drawing