


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
G	14			ZONE	LTR	DESCRIPTION	DATE	APPD
					C	REV PER 063A-0435-02	30SEP02	JR MS

DIMPLES
BRAZED SEAM



AMP WIRE RANGE	UL E13288 Listed
300-350 MCM SOLID OR STRANDED	300-350 MCM SOLID OR STRANDED
SP LR7189 Certified	MILITARY P/N AND CLASS
300-350 MCM SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP W* 300-350 MCM APPROX AS SHOWN
2 MATERIAL THK: 3.45^{±0.10} [.136^{±.004}]
3 STAMP FOR MANUFACTURING LOCATION OR CODE PERMISSIBLE.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX			322276		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE			PART NO		
FOR APPLICATION TOOLING INFORMATION			CIRCULAR MIL AREA: 152.0-192.5mm ² [300-380] MCM SOLID OR STRANDED			NAME SPLICE, PARALLEL, SOLISTRAND, WIRE SIZE: 300-350 MCM		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			SIZE B		
1-800-522-6752			1-800-722-1111			CAGE CODE 00779		
1-800-526-5142			1-800-526-5142			DRAWING NO C-322276		
						SCALE 2:1		
						SHEET 1 OF 1		