

Our new 2012 models have arrived!

Home > Phones & Home Office > Fax Machines > Fax Machines > KX-FLM671

Multifunction Network Laser Fax Machine

Model number: **KX-FLM671**

★★★★★ This product has not yet been rated. Be the first to [WRITE A REVIEW!](#)

[Print this](#) | [Share this](#)

33.6kbps Multifunction Laser Fax, w/ Built-in Ethernet

Available at your favorite retailer



[enlarge](#)



Overview | Tech Specifications | Reviews | Accessories | Operating Manuals

GENERAL SPECIFICATIONS	
Print Method	Laser
Print Speed	14 PPM
Paper Tray Capacity	250 sheets
ADF Capacity	20 sheets
Interface(s) ¹	10/100 Base-TX Ethernet Hi-Speed USB 2.0
Compatible Operating Systems	Windows 98/Windows Me/Windows 2000/Windows XP/Windows Vista®/Windows 7
Input Paper Capacity	Input Paper Capacity
2-Line, 16-character LCD Display	Yes
Fax Modem Speed	33.6 Kbps Super G3 Fax
Transmission Speed ²	4 seconds per page
Quick Scan	Yes
Data Compression System	MH/MR/MMR
Fax memory capacity	Approx. 150 pages of memory transmission Approx. 100 pages of memory reception
Out of Paper Reception ³	Yes
ECM	Yes
Dual Access	Yes
Resolution	Up to 203 x 392 dpi
One-Touch Stations	20 x 3 station
Speed Dial Stations	300 + 22 stations
Distinctive Ring Detection ⁴	Yes
Junk Fax Prohibitor	Yes
Delayed Transmission	Yes
Journal Report	Yes
Telephone Handset	Yes (Corded)
TEL/TAD/FAX Switching	Yes
Redial	Yes
Caller ID ⁵	Yes
SCAN FUNCTION	
Scanner Type	CIS
Scanning Capability	BMW Scanning
Scan Resolution	Up to 9,600 x 9,600 dpi (Interpolated)
Scan Formats	TIFF, JPEG, BMP, PDF
"Scan to" feature	Viewer/File/E-mail/OCR
Direct Scan-to-Email	Yes
PRINTER FUNCTION	
Print Emulation	GDI - Host Based
PC Print	Yes
Print Resolution	600 x 600 dpi
Paper size	LTR/LGL
COPY FUNCTION	
Memory Copy Speed	10 CPM
Resolution (Copier)	600 x 600 dpi
Multi-Copy	up to 99
Reduction Copy	25% to 400% (1% step)
Enlargement Copy	25% to 400% (1% step)
Collate/Sort/Copy	Yes
N in 1 Function	Yes
OTHER	
Power Consumption	Standby: Approx. 7.5 W Transmission: Approx. 18 W Reception: Approx. 300 W Copy: Approx. 310 W Maximum: Approx. 950 W
Dimensions (H x W x D)	14.57" x 16.93" x 18.9"
Weight	20.72 lbs
Fax Advantage Program	1-year Exchange Warranty

1. USB cable or Cat 5e Ethernet Cord not included.
2. Transmission speed is based on the ITU-T No. 1 Test Chart
3. Actual number of pages depends upon the contents of the pages and the resolution. Page capacity based upon ITU-T No. 1 test chart at standard resolution.
4. Requires subscription to fee-based phone company service.
5. Requires subscription to fee-based, caller ID phone company service(s).

You may also like



Multifunction Laser Fax Machine
Suggested Retail Price: \$189.95
KX-FLM661

[LEARN MORE >](#)



33.6Kbps Laser Fax Machine
Suggested Retail Price: \$139.95
KX-FL421

[LEARN MORE >](#)



Need assistance with your order?



Email [click here](#)



Call

1-800-405-0652
Mon-Fri 8:00 AM - 9:00 PM EST
Sat-Sun 12:00 PM - 5:00 PM EST



Live Chat [click here](#)

Recently Viewed Products



VIERA® 32" Class DT30 Series LED HDTV with 3D (31.5" Diag.)

★★★★★ [2 Reviews](#)

TC-L32DT30



VIERA® 32" Class E3 Series LED HDTV (31.5" Diag.)

★★★★★ [3 Reviews](#)

TC-L32E3



VIERA® 32" Class U3 Series LCD HDTV (31.5" Diag.)

TC-L32U3

[View more](#)

Panasonic USA



[About Panasonic](#) | [Career Opportunities](#) | [Panasonic Eco Ideas](#) | [Corporate Social Responsibility](#) | [For Investors](#) | [Press Room](#)
[Shop Panasonic](#) | [Club Panasonic](#) | [My Account](#) | [Shipping FAQs](#) | [Order Status](#) | [Accessories](#) | [Get Support](#)



Copyright ©2011 Panasonic Corporation of North America. All rights reserved. | [Panasonic Direct Store Policies](#) | [Privacy Policy](#) | [Terms of Service](#)