



15 Watt Universal Switching Adapter PSA15W Single Output Series



Features

- 0A Minimum Load
- Class B EMI
- <0.25mA Leakage Current
- Slim 1" Height

Applications

- Portable Equipment
- Peripherals and Terminals
- Low-power Computers
- Networking

Safety Approvals

- cUL/UL
- CE
- TUV
- Meeting Cal. Prop. 65

Mechanical Characteristics

- Length: 110mm (4.33in)
- Width: 65mm (2.56in)
- Height: 25.4mm (1in)
- Weight: 200g (8oz.)

Output Specifications

Model	DC Output Voltage	Load		Ripple (1) P-P (max.)	Regulation Line & Load
		Min.	Max.		
PSA15W-050	+5V	0A	2.5A	50mV	±5%
PSA15W-090	+9V	0A	1.5A	90mV	±5%
PSA15W-120	+12V	0A	1.25A	120mV	±5%
PSA15W-150	+15V	0A	1A	150mV	±5%
PSA15W-180	+18V	0A	0.8A	180mV	±5%
PSA15W-240	+24V	0A	0.625A	240mV	±5%

(1) Measured by using a 12 inch twisted pair terminated with a 10uF capacitor and 0.1uF ceramic in parallel.

PhiHong is not responsible for any error and change. Please consult the factory and visit www.phihong.com for the most up-to-date specifications.

INPUT:**AC Input Voltage Rating**

100 to 240VAC

AC Input Voltage Range

90 to 264VAC

AC Input Frequency

47 to 63Hz

Input Current

0.5A (rms) Max. @ 120VAC

0.25A (rms) Max. @ 240VAC

Leakage Current

0.25mA Max.

Inrush Current (cold)

20A for 120VAC at Max. load

40A for 240VAC at Max. load

(Cold start @ ambient 25°C)

OUTPUT:**Efficiency**

70% typical

Hold-up Time

12mS Min. @ 120VAC and Max. load

Over-voltage Protection

>130% over-voltage detection, adapter will be shut down

Over-current Protection

Output equipped with short circuit protection – auto restart

Short Circuit Protection

Output can be shorted without damage

ENVIRONMENTAL:**Temperature**

Operation 0 to +40°C

Non-operation -25 to +75°C

Humidity

Operation 5 to 80%

Emissions

FCC Class B


EN55022 Class B

Dielectric Withstand (Hi-pot) Test

Primary to Secondary: 3000VAC for 1 minute, 10mA

DC Output Connector

2.1x5.5mm Center Positive Standard

Dimension Diagram Unit: mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:

[PSA15W-050-R AND DATA SHEETS](#) [PSA15W-150-R AND DATA SHEETS](#) [PSA-15W-090](#) [PSA-15W-050 AND DATA SHEETS](#) [PSA-15W-120P](#) [PSA-15W-150 AND DATA SHEETS](#) [PSA-15W-180](#) [PSA-15W-120 AND DATA SHEETS](#) [PSA-15W-050P](#) [PSA-15W-120-2.5MM](#) [PSA-15W-240 AND DATA SHEETS](#) [PSA15W-240-R AND DATA SHEETS](#) [PSA-15W-150 CENTER NEGATIVE](#) [PSA15W-120-R AND DATA SHEETS](#)