

Models 6902**Rugged XLR (M) to XLR (F) Patch Cord: 10, 15, 20, 25 feet**

Model 6902 3-Pin XLR (M) to XLR (F) patch cord: 10, 15, 20, 25 feet.

Dramatically reduce your audio system support costs.

Features

- **Pull strength is 100 pounds. Cable handles up to 30,000 bends.**
- Handles 24 AWG cable.
- Black streamlined profile with compact shell. Rugged construction.
- Robust design. Number of insertions is at least 1000 mating cycles.

Materials**Connectors:**


- Body is die cast zinc alloy with tarnish resistant black polyester finish.
- Back shell is thermoplastic UL94V-0 modified PPE resin.
- Contacts are gold-plated brass.
- Cable clamp is UL94V-0 modified PPO resin.
- Cable bushing is thermoplastic polyurethane.

Cable:

- Belden 1172A Star quad cable. See www.belden.com for specifications.

Ordering Information

Model: 6902-*: 10 feet: -120, 15 feet: -180 feet, 20 feet: -240, 25 feet: -300.

**Specifications**

Mating cycles	1000
Dielectric strength	1400 V dc
Cable type	Belden 1172A Star Quad Audio Cable
Pull strength	Up to 100 lbs.
Cable lengths	10, 15, 20, and 25 feet.
Contact resistance	≤ 3 mΩ typical
Insulation resistance	≥ 1 GΩ
Protection class	IP40
Operating temperature	-25 °C to +75 °C
Operating voltage	33 Vrms, 70 V dc

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6902-180