





PART NUMBER	SIZE	A MAX.	B NOM.	C REF.	D NOM.
836129024	15	.935	.715	.350	.715



2-56 JACKPOST
2 PLACES



RECOMMENDED
P.C.B. LAY-OUT
.060/152 PANEL THICKNESS

2. RoHS COMPLIANT
1. REFER TO PS-83421-9000 FOR PRODUCT SPECIFICATION.
NOTES: UNLESS OTHERWISE SPECIFIED.

REDRAWN EC NO: WNA2009-0562 DRWN:RUPERT CHKD:B.RUPERT APPR: J.MURPHY	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 5:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY D.URBACH	DATE 23OCT00	TITLE CONN,COMM-D,PLUG,VERT JACKPOST,SIZE 15					
			4 PLACES	± ---	± ---	CHECKED BY D.URBACH	DATE 23OCT00						
			3 PLACES	± ---	±.005	APPROVED BY D.URBACH		DATE 23OCT00		MOLEX INCORPORATED			
			2 PLACES	± 0.13	±.010								
			1 PLACE	± 0.25	± ---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-83612-9024		SHEET NO. 1 OF 1			
			ANGULAR ± 2 °										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					