


ROUND VINYL CAPS

VINYL CAPS

Round Vinyl Caps are used for a variety of applications including color coding, dust barriers, insulators, thread protectors, paint masking, and cosmetic decoration. They are resistant to weather, moisture, oxidation and petroleum products. In addition, they will not shred, crack, or split in normal applications.




Catalog Number	Dimensions						Standard Color
	A		B		C		
	inches	mm	inches	mm	inches	mm	
3544	0.137	3.48	0.500	12.70	0.033	0.84	Black
3545	0.187	4.75	0.500	12.70	0.038	0.97	White
3546	0.250	6.35	0.625	15.88	0.043	1.09	Red
3547	0.313	7.95	0.625	15.88	0.043	1.09	Blue
3548	0.375	9.53	0.750	19.05	0.043	1.09	Yellow

Additional sizes and colors available subject to minimum order quantities.

VINYL GROMMETS

GV

Vinyl Grommets are inexpensive, flexible, and oil resistant. They have a high dielectric strength and outstanding aging qualities. The standard color is black.



Hardness Durometer: 60 +/- 5 Shore A
Tensile Strength: 1400 psi
Abrasive Resistance: Excellent
Effect of Sunlight: Slight to None
Hydro Carbon Solvent Resistance: Good
Weak Acid Resistance: No Effect
Burning Rate: Self Extinguishing

Polyethylene Catalog Number Size	Dimensions										Standard Package pcs / pkg
	A		B		C		D		E		
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	
GV-1/4	0.125	3.18	0.063	1.60	0.344	8.74	0.188	4.78	0.250	6.35	100, 1000
GV-5/16	0.188	4.78	0.063	1.60	0.438	11.13	0.219	5.56	0.313	7.95	100, 1000
GV-3/8	0.250	6.35	0.063	1.60	0.563	14.30	0.250	6.35	0.375	9.53	100, 1000
GV-7/16	0.313	7.95	0.063	1.60	0.625	15.88	0.250	6.35	0.438	11.13	100, 1000
GV-1/2	0.375	9.53	0.063	1.60	0.625	15.88	0.250	6.35	0.500	12.70	100, 1000
GV-5/8	0.500	12.70	0.063	1.60	0.813	20.65	0.281	7.14	0.625	15.88	100, 500
GV-21/32	0.391	9.93	0.125	3.18	0.844	21.44	0.375	9.53	0.656	16.66	100, 500
GV-7/8	0.625	15.88	0.063	1.60	1.125	28.58	0.281	7.14	0.875	22.23	100, 500
GV-1	0.688	17.48	0.063	1.60	1.313	33.35	0.375	9.53	1.000	25.40	100, 500
GV-1-3/8	1.000	25.40	0.125	3.18	1.750	44.45	0.500	12.70	1.375	34.93	100, 250