

■ Connectivity....for  
Business-Critical Continuity

## ***RF Cable Assembly***

### ***Fixed Length Catalog***




**JOHNSON®**

  
**EMERSON™**  
Network Power

## Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

| Connector       | Cable              | Connector Impedance (Ohms) | Frequency (GHz) | Dielectric Withstanding Voltage (Vrms) | Working Voltage (Vrms) |
|-----------------|--------------------|----------------------------|-----------------|----------------------------------------|------------------------|
| MMCX            | RG-178             | 50                         | 6               | 500 Vrms                               | 170 Vrms               |
|                 | RG-316             | 50                         | 6               | 500 Vrms                               | 170 Vrms               |
| MCX             | RG-178             | 50                         | 6               | 750 Vrms                               | 250 Vrms               |
|                 | RG-316             | 50                         | 6               | 1000 Vrms                              | 335 Vrms               |
|                 | RG-316 DS          | 50                         | 6               | 1000 Vrms                              | 335 Vrms               |
| MCX 75 Ohm      | RG-179             | 75                         | 6               | 1000 Vrms                              | 335 Vrms               |
|                 | BELDEN 735A        | 75                         | 6               | 1000 Vrms                              | 335 Vrms               |
| SMA             | RG-178             | 50                         | 12.4            | 500 Vrms                               | 170 Vrms               |
|                 | RG-316             | 50                         | 12.4            | 750 Vrms                               | 250 Vrms               |
|                 | RG-316 DS          | 50                         | 12.4            | 750 Vrms                               | 250 Vrms               |
|                 | RG-58              | 50                         | 12.4            | 1000 Vrms                              | 335 Vrms               |
|                 | RG-142             | 50                         | 12.4            | 1000 Vrms                              | 335 Vrms               |
|                 | Hand Formable .086 | 50                         | 26.5            | 1000 Vrms                              | 335 Vrms               |
|                 | Hand Formable .141 | 50                         | 26.5            | 1500 Vrms                              | 500 Vrms               |
| SMB             | RG-178             | 50                         | 4               | 750 Vrms                               | 250 Vrms               |
|                 | RG-316             | 50                         | 4               | 1000 Vrms                              | 335 Vrms               |
| SMB Mini 75 Ohm | RG-179             | 75                         | 2               | 1000 Vrms                              | 335 Vrms               |
|                 | RG-179 DS          | 75                         | 2               | 1000 Vrms                              | 335 Vrms               |
|                 | BELDEN 735A        | 75                         | 2               | 1000 Vrms                              | 335 Vrms               |
| BNC             | RG-58              | 50                         | 4               | 1500 Vrms                              | 500 Vrms               |
|                 | BELDEN 8218        | 50                         | 4               | 1500 Vrms                              | 500 Vrms               |
|                 | RG-59              | 50                         | 4               | 1500 Vrms                              | 500 Vrms               |
|                 | RG-59 PLENUM       | 50                         | 4               | 1500 Vrms                              | 500 Vrms               |
| BNC True 75 Ohm | BELDEN 8218        | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | RG-59              | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | BELDEN 8281        | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | COMMScope 735      | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | BELDEN 735A        | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | BELDEN 734A        | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
|                 | BELDEN 1694A       | 75                         | 3               | 1500 Vrms                              | 500 Vrms               |
| N               | RG-58              | 50                         | 11              | 1500 Vrms                              | 500 Vrms               |
|                 | RG-142             | 50                         | 11              | 1500 Vrms                              | 500 Vrms               |
|                 | RG-8               | 50                         | 11              | 1500 Vrms                              | 500 Vrms               |
|                 | RG-213             | 50                         | 11              | 1500 Vrms                              | 500 Vrms               |



Johnson's® cable length applies to the end of straight connectors. The length is applied to the vertical centroid of right angle connectors.



If you don't see the cable assembly you require  
we can design and manufacture one to meet  
your unique specifications!

- Voltage/Continuity Test Fixture
- Interface location gauging
- VSWR Quality Assurance Scalar Analyzer
- VSWR/TDR Engineering Vector Analyzer
- CNC Hardline Bender (Semi-Rigid cables)
- Tested to customer specifications
- Flexible cable
- Conformable cable
- Semi-rigid cable
- 0 to 40 GHz
- 50 and 75 Ohms
- Controlled impedance
- Prototype available in 2 weeks

## MMCX STRAIGHT PLUG TO MMCX STRAIGHT PLUG



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0066-006 | RG-178     | 6"           | 135-3402-001 | 135-3402-001 |
| 415-0066-012 | RG-178     | 12"          | 135-3402-001 | 135-3402-001 |
| 415-0066-018 | RG-178     | 18"          | 135-3402-001 | 135-3402-001 |
| 415-0066-024 | RG-178     | 24"          | 135-3402-001 | 135-3402-001 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0067-006 | RG-316     | 6"           | 135-3403-001 | 135-3403-001 |
| 415-0067-012 | RG-316     | 12"          | 135-3403-001 | 135-3403-001 |
| 415-0067-018 | RG-316     | 18"          | 135-3403-001 | 135-3403-001 |
| 415-0067-024 | RG-316     | 24"          | 135-3403-001 | 135-3403-001 |

## MMCX RIGHT ANGLE PLUG TO MMCX RIGHT ANGLE PLUG



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0068-006 | RG-178     | 6"           | 135-3402-101 | 135-3402-101 |
| 415-0068-012 | RG-178     | 12"          | 135-3402-101 | 135-3402-101 |
| 415-0068-018 | RG-178     | 18"          | 135-3402-101 | 135-3402-101 |
| 415-0068-024 | RG-178     | 24"          | 135-3402-101 | 135-3402-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0069-006 | RG-316     | 6"           | 135-3403-101 | 135-3403-101 |
| 415-0069-012 | RG-316     | 12"          | 135-3403-101 | 135-3403-101 |
| 415-0069-018 | RG-316     | 18"          | 135-3403-101 | 135-3403-101 |
| 415-0069-024 | RG-316     | 24"          | 135-3403-101 | 135-3403-101 |

## MMCX STRAIGHT PLUG TO SMA STRAIGHT BULKHEAD JACK



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0070-006 | RG-178     | 6"           | 135-3402-001 | 142-0302-431 |
| 415-0070-012 | RG-178     | 12"          | 135-3402-001 | 142-0302-431 |
| 415-0070-018 | RG-178     | 18"          | 135-3402-001 | 142-0302-431 |
| 415-0070-024 | RG-178     | 24"          | 135-3402-001 | 142-0302-431 |
| 415-0070-036 | RG-178     | 36"          | 135-3402-001 | 142-0302-431 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0071-006 | RG-316     | 6"           | 135-3403-001 | 142-0303-411 |
| 415-0071-012 | RG-316     | 12"          | 135-3403-001 | 142-0303-411 |
| 415-0071-018 | RG-316     | 18"          | 135-3403-001 | 142-0303-411 |
| 415-0071-024 | RG-316     | 24"          | 135-3403-001 | 142-0303-411 |
| 415-0071-036 | RG-316     | 36"          | 135-3403-001 | 142-0303-411 |

## MMCX RIGHT ANGLE PLUG TO SMA STRAIGHT BULKHEAD JACK



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0072-006 | RG-178     | 6"           | 135-3402-101 | 142-0302-431 |
| 415-0072-012 | RG-178     | 12"          | 135-3402-101 | 142-0302-431 |
| 415-0072-018 | RG-178     | 18"          | 135-3402-101 | 142-0302-431 |
| 415-0072-024 | RG-178     | 24"          | 135-3402-101 | 142-0302-431 |
| 415-0072-036 | RG-178     | 36"          | 135-3402-101 | 142-0302-431 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0073-006 | RG-316     | 6"           | 135-3403-101 | 142-0303-411 |
| 415-0073-012 | RG-316     | 12"          | 135-3403-101 | 142-0303-411 |
| 415-0073-018 | RG-316     | 18"          | 135-3403-101 | 142-0303-411 |
| 415-0073-024 | RG-316     | 24"          | 135-3403-101 | 142-0303-411 |
| 415-0073-036 | RG-316     | 36"          | 135-3403-101 | 142-0303-411 |

## MCX STRAIGHT PLUG TO MCX STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0014-006 | RG-178     | 6"           | 133-3402-021 | 133-3402-021 |
| 415-0014-012 | RG-178     | 12"          | 133-3402-021 | 133-3402-021 |
| 415-0014-018 | RG-178     | 18"          | 133-3402-021 | 133-3402-021 |
| 415-0014-024 | RG-178     | 24"          | 133-3402-021 | 133-3402-021 |
| 415-0014-030 | RG-178     | 30"          | 133-3402-021 | 133-3402-021 |
| 415-0014-036 | RG-178     | 36"          | 133-3402-021 | 133-3402-021 |
| 415-0018-006 | RG-316     | 6"           | 133-3403-001 | 133-3403-001 |
| 415-0018-012 | RG-316     | 12"          | 133-3403-001 | 133-3403-001 |
| 415-0018-018 | RG-316     | 18"          | 133-3403-001 | 133-3403-001 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0018-024 | RG-316     | 24"          | 133-3403-001 | 133-3403-001 |
| 415-0018-030 | RG-316     | 30"          | 133-3403-001 | 133-3403-001 |
| 415-0018-036 | RG-316     | 36"          | 133-3403-001 | 133-3403-001 |
| 415-0020-006 | RG-316 DS  | 6"           | 133-3404-001 | 133-3404-001 |
| 415-0020-012 | RG-316 DS  | 12"          | 133-3404-001 | 133-3404-001 |
| 415-0020-018 | RG-316 DS  | 18"          | 133-3404-001 | 133-3404-001 |
| 415-0020-024 | RG-316 DS  | 24"          | 133-3404-001 | 133-3404-001 |
| 415-0020-030 | RG-316 DS  | 30"          | 133-3404-001 | 133-3404-001 |
| 415-0020-036 | RG-316 DS  | 36"          | 133-3404-001 | 133-3404-001 |

## MCX STRAIGHT PLUG TO MCX STRAIGHT BULKHEAD JACK

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0016-006 | RG-316     | 6"           | 133-3403-001 | 133-3303-401 |
| 415-0016-012 | RG-316     | 12"          | 133-3403-001 | 133-3303-401 |
| 415-0016-018 | RG-316     | 18"          | 133-3403-001 | 133-3303-401 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0016-024 | RG-316     | 24"          | 133-3403-001 | 133-3303-401 |
| 415-0016-030 | RG-316     | 30"          | 133-3403-001 | 133-3303-401 |
| 415-0016-036 | RG-316     | 36"          | 133-3403-001 | 133-3303-401 |

## MCX STRAIGHT PLUG TO MCX RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0017-006 | RG-316     | 6"           | 133-3403-001 | 133-3403-101 |
| 415-0017-012 | RG-316     | 12"          | 133-3403-001 | 133-3403-101 |
| 415-0017-018 | RG-316     | 18"          | 133-3403-001 | 133-3403-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0017-024 | RG-316     | 24"          | 133-3403-001 | 133-3403-101 |
| 415-0017-030 | RG-316     | 30"          | 133-3403-001 | 133-3403-101 |
| 415-0017-036 | RG-316     | 36"          | 133-3403-001 | 133-3403-101 |

## MCX RIGHT ANGLE PLUG TO MCX RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0015-006 | RG-178     | 6"           | 133-3402-101 | 133-3402-101 |
| 415-0015-012 | RG-178     | 12"          | 133-3402-101 | 133-3402-101 |
| 415-0015-018 | RG-178     | 18"          | 133-3402-101 | 133-3402-101 |
| 415-0015-024 | RG-178     | 24"          | 133-3402-101 | 133-3402-101 |
| 415-0015-030 | RG-178     | 30"          | 133-3402-101 | 133-3402-101 |
| 415-0015-036 | RG-178     | 36"          | 133-3402-101 | 133-3402-101 |
| 415-0019-006 | RG-316     | 6"           | 133-3403-101 | 133-3403-101 |
| 415-0019-012 | RG-316     | 12"          | 133-3403-101 | 133-3403-101 |
| 415-0019-018 | RG-316     | 18"          | 133-3403-101 | 133-3403-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0019-024 | RG-316     | 24"          | 133-3403-101 | 133-3403-101 |
| 415-0019-030 | RG-316     | 30"          | 133-3403-101 | 133-3403-101 |
| 415-0019-036 | RG-316     | 36"          | 133-3403-101 | 133-3403-101 |
| 415-0021-006 | RG-316 DS  | 6"           | 133-3404-101 | 133-3404-101 |
| 415-0021-012 | RG-316 DS  | 12"          | 133-3404-101 | 133-3404-101 |
| 415-0021-018 | RG-316 DS  | 18"          | 133-3404-101 | 133-3404-101 |
| 415-0021-024 | RG-316 DS  | 24"          | 133-3404-101 | 133-3404-101 |
| 415-0021-030 | RG-316 DS  | 30"          | 133-3404-101 | 133-3404-101 |
| 415-0021-036 | RG-316 DS  | 36"          | 133-3404-101 | 133-3404-101 |

## MCX 75 OHM STRAIGHT PLUG TO MCX 75 OHM STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0022-006 | RG-179     | 6"           | 133-8433-001 | 133-8433-001 |
| 415-0022-012 | RG-179     | 12"          | 133-8433-001 | 133-8433-001 |
| 415-0022-018 | RG-179     | 18"          | 133-8433-001 | 133-8433-001 |
| 415-0022-024 | RG-179     | 24"          | 133-8433-001 | 133-8433-001 |
| 415-0022-030 | RG-179     | 30"          | 133-8433-001 | 133-8433-001 |
| 415-0022-036 | RG-179     | 36"          | 133-8433-001 | 133-8433-001 |



| Part Number  | Cable Type  | Cable Length | Connector A  | Connector B  |
|--------------|-------------|--------------|--------------|--------------|
| 415-0023-006 | Belden 735A | 6"           | 133-8445-001 | 133-8445-001 |
| 415-0023-012 | Belden 735A | 12"          | 133-8445-001 | 133-8445-001 |
| 415-0023-018 | Belden 735A | 18"          | 133-8445-001 | 133-8445-001 |
| 415-0023-024 | Belden 735A | 24"          | 133-8445-001 | 133-8445-001 |
| 415-0023-030 | Belden 735A | 30"          | 133-8445-001 | 133-8445-001 |
| 415-0023-036 | Belden 735A | 36"          | 133-8445-001 | 133-8445-001 |

## MCX 75 OHM RIGHT ANGLE PLUG TO MCX 75 OHM RIGHT ANGLE PLUG

| Part Number  | Cable Type  | Cable Length | Connector A  | Connector B  |
|--------------|-------------|--------------|--------------|--------------|
| 415-0024-006 | Belden 735A | 6"           | 133-8445-101 | 133-8445-101 |
| 415-0024-012 | Belden 735A | 12"          | 133-8445-101 | 133-8445-101 |
| 415-0024-018 | Belden 735A | 18"          | 133-8445-101 | 133-8445-101 |



| Part Number  | Cable Type  | Cable Length | Connector A  | Connector B  |
|--------------|-------------|--------------|--------------|--------------|
| 415-0024-024 | Belden 735A | 24"          | 133-8445-101 | 133-8445-101 |
| 415-0024-030 | Belden 735A | 30"          | 133-8445-101 | 133-8445-101 |
| 415-0024-036 | Belden 735A | 36"          | 133-8445-101 | 133-8445-101 |

## SMA STRAIGHT PLUG TO SMA STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0025-006 | RG-178     | 6"           | 142-0402-011 | 142-0402-011 |
| 415-0025-012 | RG-178     | 12"          | 142-0402-011 | 142-0402-011 |
| 415-0025-018 | RG-178     | 18"          | 142-0402-011 | 142-0402-011 |
| 415-0025-024 | RG-178     | 24"          | 142-0402-011 | 142-0402-011 |
| 415-0025-036 | RG-178     | 36"          | 142-0402-011 | 142-0402-011 |
| 415-0025-048 | RG-178     | 48"          | 142-0402-011 | 142-0402-011 |
| 415-0029-006 | RG-316     | 6"           | 142-0403-011 | 142-0403-011 |
| 415-0029-012 | RG-316     | 12"          | 142-0403-011 | 142-0403-011 |
| 415-0029-018 | RG-316     | 18"          | 142-0403-011 | 142-0403-011 |
| 415-0029-024 | RG-316     | 24"          | 142-0403-011 | 142-0403-011 |
| 415-0029-036 | RG-316     | 36"          | 142-0403-011 | 142-0403-011 |
| 415-0029-048 | RG-316     | 48"          | 142-0403-011 | 142-0403-011 |
| 415-0033-006 | RG-316 DS  | 6"           | 142-0404-011 | 142-0404-011 |
| 415-0033-012 | RG-316 DS  | 12"          | 142-0404-011 | 142-0404-011 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0033-018 | RG-316 DS  | 18"          | 142-0404-011 | 142-0404-011 |
| 415-0033-024 | RG-316 DS  | 24"          | 142-0404-011 | 142-0404-011 |
| 415-0033-036 | RG-316 DS  | 36"          | 142-0404-011 | 142-0404-011 |
| 415-0033-048 | RG-316 DS  | 48"          | 142-0404-011 | 142-0404-011 |
| 415-0038-012 | RG-58      | 12"          | 142-0407-011 | 142-0407-011 |
| 415-0038-024 | RG-58      | 24"          | 142-0407-011 | 142-0407-011 |
| 415-0038-036 | RG-58      | 36"          | 142-0407-011 | 142-0407-011 |
| 415-0038-048 | RG-58      | 48"          | 142-0407-011 | 142-0407-011 |
| 415-0038-060 | RG-58      | 60"          | 142-0407-011 | 142-0407-011 |
| 415-0043-012 | RG-142     | 12"          | 142-0408-011 | 142-0408-011 |
| 415-0043-024 | RG-142     | 24"          | 142-0408-011 | 142-0408-011 |
| 415-0043-036 | RG-142     | 36"          | 142-0408-011 | 142-0408-011 |
| 415-0043-048 | RG-142     | 48"          | 142-0408-011 | 142-0408-011 |
| 415-0043-060 | RG-142     | 60"          | 142-0408-011 | 142-0408-011 |

## HAND FORMABLE SMA STRAIGHT PLUG TO SMA STRAIGHT PLUG



| Part Number  | Cable Type         | Cable Length | Connector A  | Connector B  |
|--------------|--------------------|--------------|--------------|--------------|
| 415-0081-003 | HAND FORMABLE .086 | 3"           | 142-0693-001 | 142-0693-001 |
| 415-0081-004 | HAND FORMABLE .086 | 4"           | 142-0693-001 | 142-0693-001 |
| 415-0081-005 | HAND FORMABLE .086 | 5"           | 142-0693-001 | 142-0693-001 |
| 415-0081-006 | HAND FORMABLE .086 | 6"           | 142-0693-001 | 142-0693-001 |
| 415-0081-007 | HAND FORMABLE .086 | 7"           | 142-0693-001 | 142-0693-001 |



| Part Number  | Cable Type         | Cable Length | Connector A  | Connector B  |
|--------------|--------------------|--------------|--------------|--------------|
| 415-0081-008 | HAND FORMABLE .086 | 8"           | 142-0693-001 | 142-0693-001 |
| 415-0081-012 | HAND FORMABLE .086 | 12"          | 142-0693-001 | 142-0693-001 |
| 415-0081-018 | HAND FORMABLE .086 | 18"          | 142-0693-001 | 142-0693-001 |
| 415-0081-024 | HAND FORMABLE .086 | 24"          | 142-0693-001 | 142-0693-001 |

## HAND FORMABLE SMA STRAIGHT PLUG TO SMA STRAIGHT PLUG



| Part Number  | Cable Type         | Cable Length | Connector A  | Connector B  |
|--------------|--------------------|--------------|--------------|--------------|
| 415-0082-003 | HAND FORMABLE .141 | 3"           | 142-0694-001 | 142-0694-001 |
| 415-0082-004 | HAND FORMABLE .141 | 4"           | 142-0694-001 | 142-0694-001 |
| 415-0082-005 | HAND FORMABLE .141 | 5"           | 142-0694-001 | 142-0694-001 |
| 415-0082-006 | HAND FORMABLE .141 | 6"           | 142-0694-001 | 142-0694-001 |
| 415-0082-007 | HAND FORMABLE .141 | 7"           | 142-0694-001 | 142-0694-001 |



| Part Number  | Cable Type         | Cable Length | Connector A  | Connector B  |
|--------------|--------------------|--------------|--------------|--------------|
| 415-0082-008 | HAND FORMABLE .141 | 8"           | 142-0694-001 | 142-0694-001 |
| 415-0082-012 | HAND FORMABLE .141 | 12"          | 142-0694-001 | 142-0694-001 |
| 415-0082-018 | HAND FORMABLE .141 | 18"          | 142-0694-001 | 142-0694-001 |
| 415-0082-024 | HAND FORMABLE .141 | 24"          | 142-0694-001 | 142-0694-001 |

## SMA STRAIGHT PLUG TO SMA STRAIGHT BULKHEAD JACK

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0031-006 | RG-316     | 6"           | 142-0403-011 | 142-0303-411 |
| 415-0031-012 | RG-316     | 12"          | 142-0403-011 | 142-0303-411 |
| 415-0031-018 | RG-316     | 18"          | 142-0403-011 | 142-0303-411 |
| 415-0031-024 | RG-316     | 24"          | 142-0403-011 | 142-0303-411 |
| 415-0031-036 | RG-316     | 36"          | 142-0403-011 | 142-0303-411 |
| 415-0031-048 | RG-316     | 48"          | 142-0403-011 | 142-0303-411 |
| 415-0035-006 | RG-316 DS  | 6"           | 142-0404-011 | 142-0304-411 |
| 415-0035-012 | RG-316 DS  | 12"          | 142-0404-011 | 142-0304-411 |
| 415-0035-018 | RG-316 DS  | 18"          | 142-0404-011 | 142-0304-411 |
| 415-0035-024 | RG-316 DS  | 24"          | 142-0404-011 | 142-0304-411 |
| 415-0035-036 | RG-316 DS  | 36"          | 142-0404-011 | 142-0304-411 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0035-048 | RG-316 DS  | 48"          | 142-0404-011 | 142-0304-411 |
| 415-0040-012 | RG-58      | 12"          | 142-0407-011 | 142-0307-411 |
| 415-0040-024 | RG-58      | 24"          | 142-0407-011 | 142-0307-411 |
| 415-0040-036 | RG-58      | 36"          | 142-0407-011 | 142-0307-411 |
| 415-0040-048 | RG-58      | 48"          | 142-0407-011 | 142-0307-411 |
| 415-0040-060 | RG-58      | 60"          | 142-0407-011 | 142-0307-411 |
| 415-0045-012 | RG-142     | 12"          | 142-0408-011 | 142-0308-411 |
| 415-0045-024 | RG-142     | 24"          | 142-0408-011 | 142-0308-411 |
| 415-0045-036 | RG-142     | 36"          | 142-0408-011 | 142-0308-411 |
| 415-0045-048 | RG-142     | 48"          | 142-0408-011 | 142-0308-411 |
| 415-0045-060 | RG-142     | 60"          | 142-0408-011 | 142-0308-411 |

## SMA STRAIGHT PLUG TO SMA RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0026-006 | RG-178     | 6"           | 142-0402-011 | 142-0402-101 |
| 415-0026-012 | RG-178     | 12"          | 142-0402-011 | 142-0402-101 |
| 415-0026-018 | RG-178     | 18"          | 142-0402-011 | 142-0402-101 |
| 415-0026-024 | RG-178     | 24"          | 142-0402-011 | 142-0402-101 |
| 415-0026-036 | RG-178     | 36"          | 142-0402-011 | 142-0402-101 |
| 415-0026-048 | RG-178     | 48"          | 142-0402-011 | 142-0402-101 |
| 415-0030-006 | RG-316     | 6"           | 142-0403-011 | 142-0403-101 |
| 415-0030-012 | RG-316     | 12"          | 142-0403-011 | 142-0403-101 |
| 415-0030-018 | RG-316     | 18"          | 142-0403-011 | 142-0403-101 |
| 415-0030-024 | RG-316     | 24"          | 142-0403-011 | 142-0403-101 |
| 415-0030-036 | RG-316     | 36"          | 142-0403-011 | 142-0403-101 |
| 415-0030-048 | RG-316     | 48"          | 142-0403-011 | 142-0403-101 |
| 415-0034-006 | RG-316 DS  | 6"           | 142-0404-011 | 142-0404-101 |
| 415-0034-012 | RG-316 DS  | 12"          | 142-0404-011 | 142-0404-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0034-018 | RG-316 DS  | 18"          | 142-0404-011 | 142-0404-101 |
| 415-0034-024 | RG-316 DS  | 24"          | 142-0404-011 | 142-0404-101 |
| 415-0034-036 | RG-316 DS  | 36"          | 142-0404-011 | 142-0404-101 |
| 415-0034-048 | RG-316 DS  | 48"          | 142-0404-011 | 142-0404-101 |
| 415-0039-012 | RG-58      | 12"          | 142-0407-011 | 142-0407-101 |
| 415-0039-024 | RG-58      | 24"          | 142-0407-011 | 142-0407-101 |
| 415-0039-036 | RG-58      | 36"          | 142-0407-011 | 142-0407-101 |
| 415-0039-048 | RG-58      | 48"          | 142-0407-011 | 142-0407-101 |
| 415-0039-060 | RG-58      | 60"          | 142-0407-011 | 142-0407-101 |
| 415-0044-012 | RG-142     | 12"          | 142-0408-011 | 142-0408-101 |
| 415-0044-024 | RG-142     | 24"          | 142-0408-011 | 142-0408-101 |
| 415-0044-036 | RG-142     | 36"          | 142-0408-011 | 142-0408-101 |
| 415-0044-048 | RG-142     | 48"          | 142-0408-011 | 142-0408-101 |
| 415-0044-060 | RG-142     | 60"          | 142-0408-011 | 142-0408-101 |

## SMA RIGHT ANGLE PLUG TO SMA RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0027-006 | RG-178     | 6"           | 142-0402-101 | 142-0402-101 |
| 415-0027-012 | RG-178     | 12"          | 142-0402-101 | 142-0402-101 |
| 415-0027-018 | RG-178     | 18"          | 142-0402-101 | 142-0402-101 |
| 415-0027-024 | RG-178     | 24"          | 142-0402-101 | 142-0402-101 |
| 415-0027-036 | RG-178     | 36"          | 142-0402-101 | 142-0402-101 |
| 415-0027-048 | RG-178     | 48"          | 142-0402-101 | 142-0402-101 |
| 415-0032-006 | RG-316     | 6"           | 142-0403-101 | 142-0403-101 |
| 415-0032-012 | RG-316     | 12"          | 142-0403-101 | 142-0403-101 |
| 415-0032-018 | RG-316     | 18"          | 142-0403-101 | 142-0403-101 |
| 415-0032-024 | RG-316     | 24"          | 142-0403-101 | 142-0403-101 |
| 415-0032-036 | RG-316     | 36"          | 142-0403-101 | 142-0403-101 |
| 415-0032-048 | RG-316     | 48"          | 142-0403-101 | 142-0403-101 |
| 415-0036-006 | RG-316 DS  | 6"           | 142-0404-101 | 142-0404-101 |
| 415-0036-012 | RG-316 DS  | 12"          | 142-0404-101 | 142-0404-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0036-018 | RG-316 DS  | 18"          | 142-0404-101 | 142-0404-101 |
| 415-0036-024 | RG-316 DS  | 24"          | 142-0404-101 | 142-0404-101 |
| 415-0036-036 | RG-316 DS  | 36"          | 142-0404-101 | 142-0404-101 |
| 415-0036-048 | RG-316 DS  | 48"          | 142-0404-101 | 142-0404-101 |
| 415-0041-012 | RG-58      | 12"          | 142-0407-101 | 142-0407-101 |
| 415-0041-024 | RG-58      | 24"          | 142-0407-101 | 142-0407-101 |
| 415-0041-036 | RG-58      | 36"          | 142-0407-101 | 142-0407-101 |
| 415-0041-048 | RG-58      | 48"          | 142-0407-101 | 142-0407-101 |
| 415-0041-060 | RG-58      | 60"          | 142-0407-101 | 142-0407-101 |
| 415-0046-012 | RG-142     | 12"          | 142-0408-101 | 142-0408-101 |
| 415-0046-024 | RG-142     | 24"          | 142-0408-101 | 142-0408-101 |
| 415-0046-036 | RG-142     | 36"          | 142-0408-101 | 142-0408-101 |
| 415-0046-048 | RG-142     | 48"          | 142-0408-101 | 142-0408-101 |
| 415-0046-060 | RG-142     | 60"          | 142-0408-101 | 142-0408-101 |

## SMA RIGHT ANGLE PLUG TO SMA STRAIGHT BULKHEAD JACK

NEW

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0074-006 | RG-316     | 6"           | 142-0403-101 | 142-0303-411 |
| 415-0074-012 | RG-316     | 12"          | 142-0403-101 | 142-0303-411 |
| 415-0074-024 | RG-316     | 24"          | 142-0403-101 | 142-0303-411 |
| 415-0074-036 | RG-316     | 36"          | 142-0403-101 | 142-0303-411 |
| 415-0074-048 | RG-316     | 48"          | 142-0403-101 | 142-0303-411 |
| 415-0064-006 | RG-316 DS  | 6"           | 142-0404-101 | 142-0304-411 |
| 415-0064-012 | RG-316 DS  | 12"          | 142-0404-101 | 142-0304-411 |
| 415-0064-024 | RG-316 DS  | 24"          | 142-0404-101 | 142-0304-411 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0064-036 | RG-316 DS  | 36"          | 142-0404-101 | 142-0304-411 |
| 415-0064-048 | RG-316 DS  | 48"          | 142-0404-101 | 142-0304-411 |
| 415-0075-006 | RG-142     | 6"           | 142-0408-101 | 142-0308-411 |
| 415-0075-012 | RG-142     | 12"          | 142-0408-101 | 142-0308-411 |
| 415-0075-024 | RG-142     | 24"          | 142-0408-101 | 142-0308-411 |
| 415-0075-036 | RG-142     | 36"          | 142-0408-101 | 142-0308-411 |
| 415-0075-048 | RG-142     | 48"          | 142-0408-101 | 142-0308-411 |

## STRAIGHT SMA QUICK-CONNECT PLUG TO STRAIGHT SMA QUICK-CONNECT PLUG

NEW

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0065-006 | RG-316     | 6"           | 142-1403-001 | 142-1403-001 |
| 415-0065-012 | RG-316     | 12"          | 142-1403-001 | 142-1403-001 |
| 415-0065-018 | RG-316     | 18"          | 142-1403-001 | 142-1403-001 |
| 415-0065-024 | RG-316     | 24"          | 142-1403-001 | 142-1403-001 |
| 415-0065-036 | RG-316     | 36"          | 142-1403-001 | 142-1403-001 |
| 415-0065-048 | RG-316     | 48"          | 142-1403-001 | 142-1403-001 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0076-012 | RG-316 DS  | 12"          | 142-1404-001 | 142-1404-001 |
| 415-0076-024 | RG-316 DS  | 24"          | 142-1404-001 | 142-1404-001 |
| 415-0076-036 | RG-316 DS  | 36"          | 142-1404-001 | 142-1404-001 |
| 415-0077-012 | RG-142     | 12"          | 142-1408-001 | 142-1408-001 |
| 415-0077-024 | RG-142     | 24"          | 142-1408-001 | 142-1408-001 |
| 415-0077-036 | RG-142     | 36"          | 142-1408-001 | 142-1408-001 |

## STRAIGHT SMA QUICK-CONNECT PLUG TO STRAIGHT SMA PLUG

NEW

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0078-012 | RG-316 DS  | 12"          | 142-1404-001 | 142-0404-011 |
| 415-0078-024 | RG-316 DS  | 24"          | 142-1404-001 | 142-0404-011 |
| 415-0078-036 | RG-316 DS  | 36"          | 142-1404-001 | 142-0404-011 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0079-012 | RG-142     | 12"          | 142-1408-001 | 142-0408-011 |
| 415-0079-024 | RG-142     | 24"          | 142-1408-001 | 142-0408-011 |
| 415-0079-036 | RG-142     | 36"          | 142-1408-001 | 142-0408-011 |

## SMB STRAIGHT PLUG TO SMB STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0003-006 | RG-316     | 6"           | 131-1403-001 | 131-1403-001 |
| 415-0003-012 | RG-316     | 12"          | 131-1403-001 | 131-1403-001 |
| 415-0003-018 | RG-316     | 18"          | 131-1403-001 | 131-1403-001 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0003-024 | RG-316     | 24"          | 131-1403-001 | 131-1403-001 |
| 415-0003-030 | RG-316     | 30"          | 131-1403-001 | 131-1403-001 |
| 415-0003-036 | RG-316     | 36"          | 131-1403-001 | 131-1403-001 |

## SMB STRAIGHT PLUG TO SMB RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0007-006 | RG-178     | 6"           | 131-3402-001 | 131-1402-101 |
| 415-0007-012 | RG-178     | 12"          | 131-3402-001 | 131-1402-101 |
| 415-0007-018 | RG-178     | 18"          | 131-3402-001 | 131-1402-101 |
| 415-0007-024 | RG-178     | 24"          | 131-3402-001 | 131-1402-101 |
| 415-0007-030 | RG-178     | 30"          | 131-3402-001 | 131-1402-101 |
| 415-0007-036 | RG-178     | 36"          | 131-3402-001 | 131-1402-101 |
| 415-0002-006 | RG-316     | 6"           | 131-1403-001 | 131-1403-101 |
| 415-0002-012 | RG-316     | 12"          | 131-1403-001 | 131-1403-101 |
| 415-0002-018 | RG-316     | 18"          | 131-1403-001 | 131-1403-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0002-024 | RG-316     | 24"          | 131-1403-001 | 131-1403-101 |
| 415-0002-030 | RG-316     | 30"          | 131-1403-001 | 131-1403-101 |
| 415-0002-036 | RG-316     | 36"          | 131-1403-001 | 131-1403-101 |
| 415-0005-006 | RG-316 DS  | 6"           | 131-1404-001 | 131-1404-101 |
| 415-0005-012 | RG-316 DS  | 12"          | 131-1404-001 | 131-1404-101 |
| 415-0005-018 | RG-316 DS  | 18"          | 131-1404-001 | 131-1404-101 |
| 415-0005-024 | RG-316 DS  | 24"          | 131-1404-001 | 131-1404-101 |
| 415-0005-030 | RG-316 DS  | 30"          | 131-1404-001 | 131-1404-101 |
| 415-0005-036 | RG-316 DS  | 36"          | 131-1404-001 | 131-1404-101 |

## SMB RIGHT ANGLE PLUG TO SMB RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0001-006 | RG-178     | 6"           | 131-1402-101 | 131-1402-101 |
| 415-0001-012 | RG-178     | 12"          | 131-1402-101 | 131-1402-101 |
| 415-0001-018 | RG-178     | 18"          | 131-1402-101 | 131-1402-101 |
| 415-0001-024 | RG-178     | 24"          | 131-1402-101 | 131-1402-101 |
| 415-0001-030 | RG-178     | 30"          | 131-1402-101 | 131-1402-101 |
| 415-0001-036 | RG-178     | 36"          | 131-1402-101 | 131-1402-101 |
| 415-0004-006 | RG-316     | 6"           | 131-1403-101 | 131-1403-101 |
| 415-0004-012 | RG-316     | 12"          | 131-1403-101 | 131-1403-101 |
| 415-0004-018 | RG-316     | 18"          | 131-1403-101 | 131-1403-101 |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0004-024 | RG-316     | 24"          | 131-1403-101 | 131-1403-101 |
| 415-0004-030 | RG-316     | 30"          | 131-1403-101 | 131-1403-101 |
| 415-0004-036 | RG-316     | 36"          | 131-1403-101 | 131-1403-101 |
| 415-0006-006 | RG-316 DS  | 6"           | 131-1404-101 | 131-1404-101 |
| 415-0006-012 | RG-316 DS  | 12"          | 131-1404-101 | 131-1404-101 |
| 415-0006-018 | RG-316 DS  | 18"          | 131-1404-101 | 131-1404-101 |
| 415-0006-024 | RG-316 DS  | 24"          | 131-1404-101 | 131-1404-101 |
| 415-0006-030 | RG-316 DS  | 30"          | 131-1404-101 | 131-1404-101 |
| 415-0006-036 | RG-316 DS  | 36"          | 131-1404-101 | 131-1404-101 |

## SMB MINI-75 OHM STRAIGHT PLUG TO SMB MINI-75 OHM STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0008-006 | RG-179     | 6"           | 131-8403-011 | 131-8403-011 |
| 415-0008-012 | RG-179     | 12"          | 131-8403-011 | 131-8403-011 |
| 415-0008-018 | RG-179     | 18"          | 131-8403-011 | 131-8403-011 |
| 415-0008-024 | RG-179     | 24"          | 131-8403-011 | 131-8403-011 |
| 415-0008-030 | RG-179     | 30"          | 131-8403-011 | 131-8403-011 |
| 415-0008-036 | RG-179     | 36"          | 131-8403-011 | 131-8403-011 |
| 415-0010-006 | RG-179 DS  | 6"           | 131-8404-011 | 131-8404-011 |
| 415-0010-012 | RG-179 DS  | 12"          | 131-8404-011 | 131-8404-011 |
| 415-0010-018 | RG-179 DS  | 18"          | 131-8404-011 | 131-8404-011 |



| Part Number  | Cable Type  | Cable Length | Connector A  | Connector B  |
|--------------|-------------|--------------|--------------|--------------|
| 415-0010-024 | RG-179 DS   | 24"          | 131-8404-011 | 131-8404-011 |
| 415-0010-030 | RG-179 DS   | 30"          | 131-8404-011 | 131-8404-011 |
| 415-0010-036 | RG-179 DS   | 36"          | 131-8404-011 | 131-8404-011 |
| 415-0012-006 | Belden 735A | 6"           | 131-8445-001 | 131-8445-001 |
| 415-0012-012 | Belden 735A | 12"          | 131-8445-001 | 131-8445-001 |
| 415-0012-018 | Belden 735A | 18"          | 131-8445-001 | 131-8445-001 |
| 415-0012-024 | Belden 735A | 24"          | 131-8445-001 | 131-8445-001 |
| 415-0012-030 | Belden 735A | 30"          | 131-8445-001 | 131-8445-001 |
| 415-0012-036 | Belden 735A | 36"          | 131-8445-001 | 131-8445-001 |

## SMB MINI-75 OHM RIGHT ANGLE PLUG TO SMB MINI-75 OHM RIGHT ANGLE PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B  |
|--------------|------------|--------------|--------------|--------------|
| 415-0009-006 | RG-179     | 6"           | 131-8403-111 | 131-8403-111 |
| 415-0009-012 | RG-179     | 12"          | 131-8403-111 | 131-8403-111 |
| 415-0009-018 | RG-179     | 18"          | 131-8403-111 | 131-8403-111 |
| 415-0009-024 | RG-179     | 24"          | 131-8403-111 | 131-8403-111 |
| 415-0009-030 | RG-179     | 30"          | 131-8403-111 | 131-8403-111 |
| 415-0009-036 | RG-179     | 36"          | 131-8403-111 | 131-8403-111 |
| 415-0011-006 | RG-179 DS  | 6"           | 131-8404-111 | 131-8404-111 |
| 415-0011-012 | RG-179 DS  | 12"          | 131-8404-111 | 131-8404-111 |
| 415-0011-018 | RG-179 DS  | 18"          | 131-8404-111 | 131-8404-111 |



| Part Number  | Cable Type  | Cable Length | Connector A  | Connector B  |
|--------------|-------------|--------------|--------------|--------------|
| 415-0011-024 | RG-179 DS   | 24"          | 131-8404-111 | 131-8404-111 |
| 415-0011-030 | RG-179 DS   | 30"          | 131-8404-111 | 131-8404-111 |
| 415-0011-036 | RG-179 DS   | 36"          | 131-8404-111 | 131-8404-111 |
| 415-0013-006 | Belden 735A | 6"           | 131-8445-101 | 131-8445-101 |
| 415-0013-012 | Belden 735A | 12"          | 131-8445-101 | 131-8445-101 |
| 415-0013-018 | Belden 735A | 18"          | 131-8445-101 | 131-8445-101 |
| 415-0013-024 | Belden 735A | 24"          | 131-8445-101 | 131-8445-101 |
| 415-0013-030 | Belden 735A | 30"          | 131-8445-101 | 131-8445-101 |
| 415-0013-036 | Belden 735A | 36"          | 131-8445-101 | 131-8445-101 |

## N STRAIGHT PLUG TO N STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A | Connector B |
|--------------|------------|--------------|-------------|-------------|
| 415-0058-012 | RG-58      | 12"          | CPN-1       | CPN-1       |
| 415-0058-024 | RG-58      | 24"          | CPN-1       | CPN-1       |
| 415-0058-036 | RG-58      | 36"          | CPN-1       | CPN-1       |
| 415-0058-048 | RG-58      | 48"          | CPN-1       | CPN-1       |
| 415-0058-060 | RG-58      | 60"          | CPN-1       | CPN-1       |
| 415-0060-012 | RG-142     | 12"          | CPN-142T    | CPN-142T    |
| 415-0060-024 | RG-142     | 24"          | CPN-142T    | CPN-142T    |
| 415-0060-036 | RG-142     | 36"          | CPN-142T    | CPN-142T    |
| 415-0060-048 | RG-142     | 48"          | CPN-142T    | CPN-142T    |
| 415-0060-060 | RG-142     | 60"          | CPN-142T    | CPN-142T    |



| Part Number  | Cable Type | Cable Length | Connector A | Connector B |
|--------------|------------|--------------|-------------|-------------|
| 415-0062-012 | RG-8       | 12"          | CPN-8       | CPN-8       |
| 415-0062-024 | RG-8       | 24"          | CPN-8       | CPN-8       |
| 415-0062-036 | RG-8       | 36"          | CPN-8       | CPN-8       |
| 415-0062-048 | RG-8       | 48"          | CPN-8       | CPN-8       |
| 415-0062-060 | RG-8       | 60"          | CPN-8       | CPN-8       |
| 415-0063-012 | RG-213     | 12"          | CPN-8       | CPN-8       |
| 415-0063-024 | RG-213     | 24"          | CPN-8       | CPN-8       |
| 415-0063-036 | RG-213     | 36"          | CPN-8       | CPN-8       |
| 415-0063-048 | RG-213     | 48"          | CPN-8       | CPN-8       |
| 415-0063-060 | RG-213     | 60"          | CPN-8       | CPN-8       |

## BNC STRAIGHT PLUG TO BNC STRAIGHT PLUG

With Boot

| Part Number  | Cable Type | Cable Length | Connector A | Connector B |
|--------------|------------|--------------|-------------|-------------|
| 415-0054-012 | RG-58      | 12"          | CPMC-88-1   | CPMC-88-1   |
| 415-0054-024 | RG-58      | 24"          | CPMC-88-1   | CPMC-88-1   |
| 415-0054-036 | RG-58      | 36"          | CPMC-88-1   | CPMC-88-1   |
| 415-0054-048 | RG-58      | 48"          | CPMC-88-1   | CPMC-88-1   |
| 415-0054-060 | RG-58      | 60"          | CPMC-88-1   | CPMC-88-1   |
| 415-0055-012 | RG-59 TFE  | 12"          | CPMC-88-10  | CPMC-88-10  |
| 415-0055-024 | RG-59 TFE  | 24"          | CPMC-88-10  | CPMC-88-10  |
| 415-0055-036 | RG-59 TFE  | 36"          | CPMC-88-10  | CPMC-88-10  |
| 415-0055-048 | RG-59 TFE  | 48"          | CPMC-88-10  | CPMC-88-10  |
| 415-0055-060 | RG-59 TFE  | 60"          | CPMC-88-10  | CPMC-88-10  |



With Boot

| Part Number             | Cable Type  | Cable Length | Connector A | Connector B |
|-------------------------|-------------|--------------|-------------|-------------|
| 415-0057-012            | RG-59       | 12"          | CPMC-88-2   | CPMC-88-2   |
| 415-0057-024            | RG-59       | 24"          | CPMC-88-2   | CPMC-88-2   |
| 415-0057-036            | RG-59       | 36"          | CPMC-88-2   | CPMC-88-2   |
| 415-0057-048            | RG-59       | 48"          | CPMC-88-2   | CPMC-88-2   |
| 415-0057-060            | RG-59       | 60"          | CPMC-88-2   | CPMC-88-2   |
| <b>With Heat Shrink</b> |             |              |             |             |
| 415-0056-012            | Belden 8218 | 12"          | CPMC-88-18  | CPMC-88-18  |
| 415-0056-024            | Belden 8218 | 24"          | CPMC-88-18  | CPMC-88-18  |
| 415-0056-036            | Belden 8218 | 36"          | CPMC-88-18  | CPMC-88-18  |
| 415-0056-048            | Belden 8218 | 48"          | CPMC-88-18  | CPMC-88-18  |
| 415-0056-060            | Belden 8218 | 60"          | CPMC-88-18  | CPMC-88-18  |

## 75 OHM BNC STRAIGHT PLUG TO 75 OHM BNC STRAIGHT PLUG

With Boot

| Part Number  | Cable Type  | Cable Length | Connector A | Connector B |
|--------------|-------------|--------------|-------------|-------------|
| 415-0048-012 | RG-59       | 12"          | CPMC-68-2   | CPMC-68-2   |
| 415-0048-024 | RG-59       | 24"          | CPMC-68-2   | CPMC-68-2   |
| 415-0048-036 | RG-59       | 36"          | CPMC-68-2   | CPMC-68-2   |
| 415-0048-048 | RG-59       | 48"          | CPMC-68-2   | CPMC-68-2   |
| 415-0048-060 | RG-59       | 60"          | CPMC-68-2   | CPMC-68-2   |
| 415-0052-012 | Belden 734A | 12"          | CPMC-68-35  | CPMC-68-35  |
| 415-0052-024 | Belden 734A | 24"          | CPMC-68-35  | CPMC-68-35  |
| 415-0052-036 | Belden 734A | 36"          | CPMC-68-35  | CPMC-68-35  |
| 415-0052-048 | Belden 734A | 48"          | CPMC-68-35  | CPMC-68-35  |
| 415-0052-060 | Belden 734A | 60"          | CPMC-68-35  | CPMC-68-35  |



With Heat Shrink

| Part Number  | Cable Type    | Cable Length | Connector A | Connector B |
|--------------|---------------|--------------|-------------|-------------|
| 415-0047-012 | Belden 8218   | 12"          | CPMC-68-18  | CPMC-68-18  |
| 415-0047-024 | Belden 8218   | 24"          | CPMC-68-18  | CPMC-68-18  |
| 415-0047-036 | Belden 8218   | 36"          | CPMC-68-18  | CPMC-68-18  |
| 415-0047-048 | Belden 8218   | 48"          | CPMC-68-18  | CPMC-68-18  |
| 415-0047-060 | Belden 8218   | 60"          | CPMC-68-18  | CPMC-68-18  |
| 415-0049-012 | Belden 8281   | 12"          | CPMC-68-3   | CPMC-68-3   |
| 415-0049-024 | Belden 8281   | 24"          | CPMC-68-3   | CPMC-68-3   |
| 415-0049-036 | Belden 8281   | 36"          | CPMC-68-3   | CPMC-68-3   |
| 415-0049-048 | Belden 8281   | 48"          | CPMC-68-3   | CPMC-68-3   |
| 415-0049-060 | Belden 8281   | 60"          | CPMC-68-3   | CPMC-68-3   |
| 415-0050-012 | COMMSCOPE 735 | 12"          | CPMC-68-33  | CPMC-68-33  |
| 415-0050-024 | COMMSCOPE 735 | 24"          | CPMC-68-33  | CPMC-68-33  |
| 415-0050-036 | COMMSCOPE 735 | 36"          | CPMC-68-33  | CPMC-68-33  |
| 415-0050-048 | COMMSCOPE 735 | 48"          | CPMC-68-33  | CPMC-68-33  |
| 415-0050-060 | COMMSCOPE 735 | 60"          | CPMC-68-33  | CPMC-68-33  |
| 415-0051-012 | Belden 735A   | 12"          | CPMC-68-33  | CPMC-68-33  |
| 415-0051-024 | Belden 735A   | 24"          | CPMC-68-33  | CPMC-68-33  |
| 415-0051-036 | Belden 735A   | 36"          | CPMC-68-33  | CPMC-68-33  |
| 415-0051-048 | Belden 735A   | 48"          | CPMC-68-33  | CPMC-68-33  |
| 415-0051-060 | Belden 735A   | 60"          | CPMC-68-33  | CPMC-68-33  |
| 415-0053-012 | Belden 1694A  | 12"          | CPMC-68-45  | CPMC-68-45  |
| 415-0053-024 | Belden 1694A  | 24"          | CPMC-68-45  | CPMC-68-45  |
| 415-0053-036 | Belden 1694A  | 36"          | CPMC-68-45  | CPMC-68-45  |
| 415-0053-048 | Belden 1694A  | 48"          | CPMC-68-45  | CPMC-68-45  |
| 415-0053-060 | Belden 1694A  | 60"          | CPMC-68-45  | CPMC-68-45  |



## SMA STRAIGHT PLUG TO BNC STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B |
|--------------|------------|--------------|--------------|-------------|
| 415-0028-006 | RG-316     | 6"           | 142-0403-011 | CPM-88-19   |
| 415-0028-012 | RG-316     | 12"          | 142-0403-011 | CPM-88-19   |
| 415-0028-018 | RG-316     | 18"          | 142-0403-011 | CPM-88-19   |
| 415-0028-024 | RG-316     | 24"          | 142-0403-011 | CPM-88-19   |
| 415-0028-036 | RG-316     | 36"          | 142-0403-011 | CPM-88-19   |
| 415-0028-048 | RG-316     | 48"          | 142-0403-011 | CPM-88-19   |
| 415-0037-012 | RG-58      | 12"          | 142-0407-011 | CPMC-88-1   |
| 415-0037-024 | RG-58      | 24"          | 142-0407-011 | CPMC-88-1   |

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B |
|--------------|------------|--------------|--------------|-------------|
| 415-0037-036 | RG-58      | 36"          | 142-0407-011 | CPMC-88-1   |
| 415-0037-048 | RG-58      | 48"          | 142-0407-011 | CPMC-88-1   |
| 415-0037-060 | RG-58      | 60"          | 142-0407-011 | CPMC-88-1   |
| 415-0042-012 | RG-142     | 12"          | 142-0408-011 | CPMC-88-13  |
| 415-0042-024 | RG-142     | 24"          | 142-0408-011 | CPMC-88-13  |
| 415-0042-036 | RG-142     | 36"          | 142-0408-011 | CPMC-88-13  |
| 415-0042-048 | RG-142     | 48"          | 142-0408-011 | CPMC-88-13  |
| 415-0042-060 | RG-142     | 60"          | 142-0408-011 | CPMC-88-13  |

## SMA STRAIGHT PLUG TO N STRAIGHT PLUG

| Part Number  | Cable Type | Cable Length | Connector A  | Connector B |
|--------------|------------|--------------|--------------|-------------|
| 415-0059-012 | RG-58      | 12"          | 142-0407-011 | CPN-1       |
| 415-0059-024 | RG-58      | 24"          | 142-0407-011 | CPN-1       |
| 415-0059-036 | RG-58      | 36"          | 142-0407-011 | CPN-1       |
| 415-0059-048 | RG-58      | 48"          | 142-0407-011 | CPN-1       |
| 415-0059-060 | RG-58      | 60"          | 142-0407-011 | CPN-1       |



| Part Number  | Cable Type | Cable Length | Connector A  | Connector B |
|--------------|------------|--------------|--------------|-------------|
| 415-0061-012 | RG-142     | 12"          | 142-0408-011 | CPN-142T    |
| 415-0061-024 | RG-142     | 24"          | 142-0408-011 | CPN-142T    |
| 415-0061-036 | RG-142     | 36"          | 142-0408-011 | CPN-142T    |
| 415-0061-048 | RG-142     | 48"          | 142-0408-011 | CPN-142T    |
| 415-0061-060 | RG-142     | 60"          | 142-0408-011 | CPN-142T    |

## Emerson Network Power Connectivity Solutions

**Johnson**  
**299 Johnson Avenue**  
**Waseca, MN 56093**  
**USA**

**Tel: 800.247.8256**

**Fax: 507.833.6287**

**[www.EmersonNetworkPower.com/Connectivity](http://www.EmersonNetworkPower.com/Connectivity)**

## About Emerson Network Power Connectivity Solutions

Emerson Network Power Connectivity Solutions, an Emerson business, serves the needs of wireless communications, telephony and data networks, CATV, security systems, health care and industrial facilities with a full spectrum of broadband copper and fiber optic connectivity products. For more information, visit [www.EmersonNetworkPower.com/Connectivity](http://www.EmersonNetworkPower.com/Connectivity).

## About Emerson

Emerson (NYSE: EMR), based in St. Louis, is a global leader in bringing technology and engineering together to provide innovative solutions to customers through its network power, process management, industrial automation, climate technologies, and appliance and tools businesses. Sales in fiscal 2005 were \$17.3 billion. For more information, visit [www.gotoemerson.com](http://www.gotoemerson.com).

## Emerson Network Power.

The global leader in enabling business-critical continuity.

- |                    |                                |                                |
|--------------------|--------------------------------|--------------------------------|
| ■ AC Power Systems | ■ Embedded Power               | ■ Outside Plant                |
| ■ Connectivity     | ■ Inbound Power                | ■ Precision Cooling            |
| ■ DC Power Systems | ■ Integrated Cabinet Solutions | ■ Site Monitoring and Services |

**EmersonNetworkPower.com**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Emerson Connectivity Solutions:](#)

[415-0071-006](#)