



# Ty-Rap®

**Standard**

**T&B Catalog Number:**

TY29MX

**UPC Number:**

78621083068

**Status:**

Active

**Description:**

Cable Tie 120lb 30" Ultraviolet Resistant Black Nylon with Stainless Steel Locking Device Bulk Pack, Military Specified (MIL-SPEC MS3367-6-0)

## Features

Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

## General

|          |                             |
|----------|-----------------------------|
| Material | Nylon 6.6 Weather Resistant |
| Color    | Black                       |

## Dimension Information

|                                    |      |
|------------------------------------|------|
| Nominal Length (inches)            | 30   |
| Length (inches)                    | 30   |
| Width (inches)                     | .270 |
| Max. Wire Bundle Diameter (inches) | 9    |

## Specifications

|                            |                |
|----------------------------|----------------|
| Military Standard Part No. | MS3367-6       |
| Temperature Rating         | -40°F to 185°F |
| Flammability Rating        | UL 94 V-2      |

## Tooling

|                   |               |
|-------------------|---------------|
| Application Tools | ERG120, WT197 |
|-------------------|---------------|

## Packaging

|                    |      |
|--------------------|------|
| T&B Order Multiple | 500  |
| Package in Units   | 500  |
| Package Type       | Bulk |
| T&B Sold in UOM    | Each |

|                    |                   |
|--------------------|-------------------|
| T&B Weight Per UOM | 2.26 lbs. per 100 |
|--------------------|-------------------|

#### Application Support

|                    |            |
|--------------------|------------|
| T&B Sales Drawings | wsd-000280 |
|--------------------|------------|

|          |                      |
|----------|----------------------|
| Overview | Available on Website |
|----------|----------------------|

|                          |                      |
|--------------------------|----------------------|
| Material Selection Guide | Available on Website |
|--------------------------|----------------------|

|                  |                      |
|------------------|----------------------|
| Available Colors | Available on Website |
|------------------|----------------------|

#### Certifications

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

#### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)