



[Home](#) > [Processor Spec Finder Home](#) >

Intel® Pentium® D Processor 925

[How Do I Use This Tool?](#) [Printer Friendly Format](#)

Processor Specifications:

sSpec Number: SL9D9	Package Type: LGA775
CPU Speed: 3 GHz	Manufacturing Technology: 65 nm
PCG: 05A	Core Stepping: C1
Bus Speed: 800 MHz	CPUID String: 0F64h
Bus/Core Ratio: 15.0	Thermal Design Power: 95W
L2 Cache Size: 4 MB (2x2)	Thermal Specification: 63.4°C
L2 Cache Speed: 3 GHz	VID Voltage Range: 1.225V-1.325V

Product Documentation:

<http://support.intel.com/support/processors/pentiumd/index.htm>

Product Order Codes:

Box Order Code: BX80553925

OEM Order Code: HH80553PG0804MN

Supported Features:

- Dual Core
- Enhanced Intel Speedstep® Technology
- Intel® EM64T ¹
- Enhanced Halt State (C1E)
- Execute Disable Bit ²

Notes:

Legal Disclaimers:

1 Intel® EM64T requires a computer system with a processor, chipset, BIOS, operating system, device drivers and applications enabled for Intel EM64T. Processor will not operate (including 32-bit operation) without an Intel EM64T-enabled BIOS. Performance will vary depending on your hardware and software configurations. See <http://www.intel.com/info/em64t> for more information including details on which processors support Intel® EM64T or consult with your system vendor for more information.

2 Enabling Execute Disable Bit functionality requires a PC with a processor with Execute Disable Bit capability and a supporting operating system. Check with your PC manufacturer on whether your system delivers Execute Disable Bit functionality.