










## 95 61 190 Wire Rope Cutter



- Technical details
- Description

<b>No.</b>	95 61 190	
<b>EAN</b>	4003773040651	
<b>Head</b>	polished	
<b>Handles</b>	plastic coated	
	10.00	mm <sup>2</sup>
	6.00	Ø mm
	6.00	Ø mm
	4.00	Ø mm
	4.00	Ø mm
	7.00	Ø mm
	2.50	Ø mm
<b>AWG</b>	7	
	190	mm
	314	g

- for medium hard wire up to 6 mmdia., e.g. Bowden cords, but also for cables and steel rods
- with opening spring and locking lever
- cutting edges additionally induction hardened
- special blade geometry prevents the wire rope fanning out
- High-grade special tool steel, forged, oil-hardened

technical change and errors excepted