

Aven Inc.
4595 Platt Rd.
Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • **Web Address:** www.aventools.com

[All Categories](#) > [Hand Tools](#) > [Tweezers and Smart Tweezers](#) > [Ceramic Tweezers](#) > [Item # 18810](#)

Item # 18810, Accu-Tek Pattern 71 Tweezer



Zirconia ceramic tips. Contamination free. Temperature resistant to 1500 degree C. Solder and wear resistant. Stainless Steel handles.

Straight fine smooth tips

[larger image](#)

[Features](#) · [Specifications](#)

Features

- Extremely smooth surface and very low coefficient of friction.
- Low thermal conductivity and high thermal shock resistance.
- Excellent electric loss at very high frequency range (VHF, UHF, and SHF).
- Will not cause electromagnetic induction or eddy current loss in high frequency.
- 100% non magnetic, non rusting and non static.
- Highly resistant to all strong acids except hydrofluoric.
- Free from all metallic contamination.
- Solder will not adhere to surface.
- Six times harder than stainless steel.
- Two times harder than carbon steel.
- Will hold tip geometry better than metal.
- Can be subject to microwaves for sterilization.
- Thermal insulators well suited for soldering.
- Resistant to 1500°C

Specifications

Tip	Straight fine smooth tips
Pattern	71
Length	5 1/4 in
Resistant Temperature	1500 °C
Weight	0.05 lb

[Print](#) [Back](#)