


Abbr.	TOLERANCE	
	P=0.5	P=1.0
P	±0.05	±0.08
Pt	±0.08	±0.10
W	±0.08	±0.10
M	±0.08	±0.12
Cw	±0.02	±0.03
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm	

RoHS Compliant			
I	05-AUG-15	TEMPERATURE	AK
H	21-JAN-13	CT DIM	QL
REV	DATE	FILE	BY



No. of PIN	Dimension												
	P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	Ft±0.01	St±0.01
XX *****	1.0	(XX - 1) x P	LLL *****	(XX + 1) x P	1.0	0.70	0.035	5.0	5.0	10.0	10.0	0.043	0.225

PROJECTION: 	GENERAL TOLERANCE $.X = +/_{0.2}$ $.XX = +/_{0.15}$		
APPROVAL: GMo	UNIT: MM SCALE: SHEET: 1/2 DRAW: CH	DESCRIPTION: 1.00MM FLAT FLEXIBLE CABLE TYPE 1 XX NB OF PIN: / LLL OVERALL LENGTH: MM WERI PART NO: 686 6 001 X X I I I	SIZE A4

