




| PANDUIT<br>PART NO. * | BUNDLE DIA.     |                 | A<br>in (mm)  | B<br>in (mm)  | C<br>in (mm)  | D<br>in (mm)  | E<br>in (mm)  | F<br>in (mm)  | MIN. LOOP<br>TENSILE lbs.<br>(N) | CROSS<br>SECTION | TIP<br>STYLE | WEIGHT<br>lbs./100 pcs.<br>(g) |
|-----------------------|-----------------|-----------------|---------------|---------------|---------------|---------------|---------------|---------------|----------------------------------|------------------|--------------|--------------------------------|
|                       | MIN. in<br>(mm) | MAX. in<br>(mm) |               |               |               |               |               |               |                                  |                  |              |                                |
| PLT3I                 | .06<br>(1.5)    | 3.00<br>(76)    | .052<br>(1.3) | .145<br>(3.7) | .220<br>(5.6) | .180<br>(4.6) | .260<br>(6.6) | 11.4<br>(290) | 40<br>(178)                      | INTERMEDIATE     | CURVED       | .32<br>(145)                   |
| PLT4I                 | .06<br>(1.5)    | 4.00<br>(102)   | .052<br>(1.3) | .145<br>(3.7) | .220<br>(5.6) | .180<br>(4.6) | .260<br>(6.6) | 14.5<br>(368) | 40<br>(178)                      | INTERMEDIATE     | CURVED       | .40<br>(181)                   |
| PLT1S                 | .06<br>(1.5)    | 1.00<br>(25)    | .052<br>(1.3) | .190<br>(4.8) | .262<br>(6.7) | .220<br>(5.6) | .316<br>(8.0) | 4.8<br>(122)  | 50<br>(222)                      | STANDARD         | CURVED       | .13<br>(58)                    |
| PLT1.5S               | .06<br>(1.5)    | 1.50<br>(38)    | .052<br>(1.3) | .190<br>(4.8) | .262<br>(6.7) | .220<br>(5.6) | .316<br>(8.0) | 6.2<br>(157)  | 50<br>(222)                      | STANDARD         | CURVED       | .26<br>(118)                   |
| PLT2S                 | .06<br>(1.5)    | 1.88<br>(47.8)  | .052<br>(1.3) | .190<br>(4.8) | .262<br>(6.7) | .220<br>(5.6) | .316<br>(8.0) | 7.4<br>(188)  | 50<br>(222)                      | STANDARD         | CURVED       | .29<br>(132)                   |
| PLT2.5S               | .06<br>(1.5)    | 2.50<br>(63.5)  | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6) | 9.8<br>(249)  | 50<br>(222)                      | STANDARD         | CURVED       | .38<br>(173)                   |
| PLT3S                 | .06<br>(1.5)    | 3.00<br>(76)    | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6) | 11.5<br>(292) | 50<br>(222)                      | STANDARD         | CURVED       | .45<br>(204)                   |

**NOTES:**

\*1) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

|     |         |     |     |      |                                                        |            |
|-----|---------|-----|-----|------|--------------------------------------------------------|------------|
|     |         |     |     |      |                                                        |            |
|     |         |     |     |      |                                                        |            |
|     |         |     |     |      |                                                        |            |
|     |         |     |     |      |                                                        |            |
|     |         |     |     |      |                                                        |            |
|     |         |     |     |      |                                                        |            |
| 31  | 8/13/13 | BWG | KJM | RTFI | CORRECTED REV NO. REMOVED NOTE 1. SEE ECN FOR DETAILS. | SS-5540/30 |
| REV | DATE    | BY  | CHK | APR  | DESCRIPTION                                            | ECN        |

|                                                                                                                                     |                         |                   |                               |                  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|-------------------------|-------------------|-------------------------------|------------------|--|
| TITLE<br><b>PAN-TY CABLE TIES - PLT SERIES</b>                                                                                      |                         |                   |                               |                  |  |
| CUSTOMER DRAWING                                                                                                                    |                         |                   |                               |                  |  |
| ITEM REVISION NAME<br><b>W10001CB/31</b>                                                                                            |                         |                   | <b>PANDUIT</b>                |                  |  |
| DATASET FILE NAME<br><b>W10001CB/31 SS-5540 SH2</b>                                                                                 |                         |                   |                               |                  |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [mm]<br>.x : - - - .xxx ± .020 [.51]<br>.xx ± .02 [.5] ANGLES : - - - |                         |                   | MATERIAL:<br><b>NYLON 6.6</b> |                  |  |
| DRAWING NUMBER:<br><b>SS-5540 SHEET 2</b>                                                                                           |                         |                   |                               |                  |  |
| DRAWN BY<br><b>CEW</b>                                                                                                              | DATE<br><b>12-27-84</b> | CHK<br><b>HVP</b> | SCALE<br><b>NONE</b>          | SHT 1 OF 1       |  |
|                                                                                                                                     |                         |                   |                               | SIZE<br><b>A</b> |  |

D101000A/16