

**Part Number: 87911-3614**

2.54mm CGrid Hdr DRSW RA 2.5SnLF 36Ckt

Image not available

Status: Active
Series: [87911](#)
Category: Molex Parts

Series image - Reference only

Product Environmental Compliance**EU RoHS:** ELV and RoHS Compliant**China RoHS:****REACH SVHC:** Contains SVHC: No**Low-Halogen Status:** Not Reviewed**Part Detail****General****Status**

Category

Series

Physical

Flammability 94V-0

Agency Certification

UL E29179

Solder Process Data

Duration at Max. Process Temperature (seconds)	14
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	265

Material Info

UPC 884982052048

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)