




F

D

D

A

	10	9	8	7	6	5	4	3	2	1		
F	TIN OPTION											F
</												

F

D

r

D

- D

A

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																																					
F	TIN OPTION										F																																																																																																																																																																																																																																																																																																																																																																																																																				
E	<table><tr><td colspan="3"></td><td colspan="6">P.C.TAIL DIMENSION 'C' = 3.00</td><td colspan="6">P.C.TAIL DIMENSION 'C' = 1.91</td></tr><tr><td rowspan="2">CKT SIZE</td><td rowspan="2">DIM 'A'</td><td rowspan="2">DIM 'B'</td><td colspan="2">PLATING OPTION 5</td><td colspan="2">PLATING OPTION 4</td><td colspan="2">PLATING OPTION 6</td><td colspan="2">PLATING OPTION 5</td><td colspan="2">PLATING OPTION 4</td><td colspan="2">PLATING OPTION 6</td></tr><tr><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td><td colspan="2">ITEM NO.</td></tr><tr><td>04</td><td>(4.19)</td><td>(2.00)</td><td></td><td>79107-7001</td><td></td><td>79107-7051</td><td>X</td><td>79107-7126</td><td></td><td>79107-7201</td><td></td><td>79107-7251</td><td>X</td><td>79107-7326</td></tr><tr><td>06</td><td>(6.19)</td><td>(4.00)</td><td></td><td>79107-7002</td><td></td><td>79107-7052</td><td>X</td><td>79107-7127</td><td></td><td>79107-7202</td><td></td><td>79107-7252</td><td>X</td><td>79107-7327</td></tr><tr><td>08</td><td>(8.19)</td><td>(6.00)</td><td></td><td>79107-7003</td><td></td><td>79107-7053</td><td>X</td><td>79107-7128</td><td></td><td>79107-7203</td><td></td><td>79107-7253</td><td>X</td><td>79107-7328</td></tr><tr><td>10</td><td>(10.19)</td><td>(8.00)</td><td></td><td>79107-7004</td><td></td><td>79107-7054</td><td>X</td><td>79107-7129</td><td></td><td>79107-7204</td><td></td><td>79107-7254</td><td>X</td><td>79107-7329</td></tr><tr><td>12</td><td>(12.19)</td><td>(10.00)</td><td></td><td>79107-7005</td><td></td><td>79107-7055</td><td></td><td>79107-7130</td><td></td><td>79107-7205</td><td></td><td>79107-7255</td><td></td><td>79107-7330</td></tr><tr><td>14</td><td>(14.19)</td><td>(12.00)</td><td></td><td>79107-7006</td><td></td><td>79107-7056</td><td>X</td><td>79107-7131</td><td></td><td>79107-7206</td><td></td><td>79107-7256</td><td>X</td><td>79107-7331</td></tr><tr><td>16</td><td>(16.19)</td><td>(14.00)</td><td></td><td>79107-7007</td><td></td><td>79107-7057</td><td>X</td><td>79107-7132</td><td></td><td>79107-7207</td><td></td><td>79107-7257</td><td>X</td><td>79107-7332</td></tr><tr><td>18</td><td>(18.19)</td><td>(16.00)</td><td></td><td>79107-7008</td><td></td><td>79107-7058</td><td>X</td><td>79107-7133</td><td></td><td>79107-7208</td><td></td><td>79107-7258</td><td>X</td><td>79107-7333</td></tr><tr><td>20</td><td>(20.19)</td><td>(18.00)</td><td></td><td>79107-7009</td><td></td><td>79107-7059</td><td>X</td><td>79107-7134</td><td></td><td>79107-7209</td><td></td><td>79107-7259</td><td>X</td><td>79107-7334</td></tr><tr><td>22</td><td>(22.19)</td><td>(20.00)</td><td></td><td>79107-7010</td><td></td><td>79107-7060</td><td>X</td><td>79107-7135</td><td></td><td>79107-7210</td><td></td><td>79107-7260</td><td>X</td><td>79107-7335</td></tr><tr><td>24</td><td>(24.19)</td><td>(22.00)</td><td></td><td>79107-7011</td><td></td><td>79107-7061</td><td>X</td><td>79107-7136</td><td></td><td>79107-7211</td><td></td><td>79107-7261</td><td>X</td><td>79107-7336</td></tr><tr><td>26</td><td>(26.19)</td><td>(24.00)</td><td></td><td>79107-7012</td><td></td><td>79107-7062</td><td>X</td><td>79107-7137</td><td></td><td>79107-7212</td><td></td><td>79107-7262</td><td>X</td><td>79107-7337</td></tr><tr><td>28</td><td>(28.19)</td><td>(26.00)</td><td></td><td>79107-7013</td><td></td><td>79107-7063</td><td>X</td><td>79107-7138</td><td></td><td>79107-7213</td><td></td><td>79107-7263</td><td>X</td><td>79107-7338</td></tr><tr><td>30</td><td>(30.19)</td><td>(28.00)</td><td></td><td>79107-7014</td><td></td><td>79107-7064</td><td>X</td><td>79107-7139</td><td></td><td>79107-7214</td><td></td><td>79107-7264</td><td>X</td><td>79107-7339</td></tr><tr><td>32</td><td>(32.19)</td><td>(30.00)</td><td></td><td>79107-7015</td><td></td><td>79107-7065</td><td>X</td><td>79107-7140</td><td></td><td>79107-7215</td><td></td><td>79107-7265</td><td>X</td><td>79107-7340</td></tr><tr><td>34</td><td>(34.19)</td><td>(32.00)</td><td></td><td>79107-7016</td><td></td><td>79107-7066</td><td>X</td><td>79107-7141</td><td></td><td>79107-7216</td><td></td><td>79107-7266</td><td>X</td><td>79107-7341</td></tr><tr><td>36</td><td>(36.19)</td><td>(34.00)</td><td></td><td>79107-7017</td><td></td><td>79107-7067</td><td>X</td><td>79107-7142</td><td></td><td>79107-7217</td><td></td><td>79107-7267</td><td>X</td><td>79107-7342</td></tr><tr><td>38</td><td>(38.19)</td><td>(36.00)</td><td></td><td>79107-7018</td><td></td><td>79107-7068</td><td>X</td><td>79107-7143</td><td></td><td>79107-7218</td><td></td><td>79107-7268</td><td>X</td><td>79107-7343</td></tr><tr><td>40</td><td>(40.19)</td><td>(38.00)</td><td></td><td>79107-7019</td><td></td><td>79107-7069</td><td>X</td><td>79107-7144</td><td></td><td>79107-7219</td><td></td><td>79107-7269</td><td>X</td><td>79107-7344</td></tr><tr><td>42</td><td>(42.19)</td><td>(40.00)</td><td></td><td>79107-7020</td><td></td><td>79107-7070</td><td>X</td><td>79107-7145</td><td></td><td>79107-7220</td><td></td><td>79107-7270</td><td>X</td><td>79107-7345</td></tr><tr><td>44</td><td>(44.19)</td><td>(42.00)</td><td></td><td>79107-7021</td><td></td><td>79107-7071</td><td>X</td><td>79107-7146</td><td></td><td>79107-7221</td><td></td><td>79107-7271</td><td>X</td><td>79107-7346</td></tr><tr><td>46</td><td>(46.19)</td><td>(44.00)</td><td></td><td>79107-7022</td><td></td><td>79107-7072</td><td>X</td><td>79107-7147</td><td></td><td>79107-7222</td><td></td><td>79107-7272</td><td>X</td><td>79107-7347</td></tr><tr><td>48</td><td>(48.19)</td><td>(46.00)</td><td></td><td>79107-7023</td><td></td><td>79107-7073</td><td>X</td><td>79107-7148</td><td></td><td>79107-7223</td><td></td><td>79107-7273</td><td>X</td><td>79107-7348</td></tr><tr><td>50</td><td>(50.19)</td><td>(48.00)</td><td></td><td>79107-7024</td><td></td><td>79107-7074</td><td>X</td><td>79107-7149</td><td></td><td>79107-7224</td><td></td><td>79107-7274</td><td>X</td><td>79107-7349</td></tr></table>															P.C.TAIL DIMENSION 'C' = 3.00						P.C.TAIL DIMENSION 'C' = 1.91						CKT SIZE	DIM 'A'	DIM 'B'	PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326	06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327	08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203		79107-7253	X	79107-7328	10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329	12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330	14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331	16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207		79107-7257	X	79107-7332	18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333	20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334	22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335	24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336	26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337	28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338	30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339	32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340	34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341	36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342	38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343	40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344	42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345	44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346	46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347	48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348	50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349	E
			P.C.TAIL DIMENSION 'C' = 3.00						P.C.TAIL DIMENSION 'C' = 1.91																																																																																																																																																																																																																																																																																																																																																																																																																						
CKT SIZE	DIM 'A'	DIM 'B'	PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6																																																																																																																																																																																																																																																																																																																																																																																																																		
			ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.																																																																																																																																																																																																																																																																																																																																																																																																																		
04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326																																																																																																																																																																																																																																																																																																																																																																																																																	
06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327																																																																																																																																																																																																																																																																																																																																																																																																																	
08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203		79107-7253	X	79107-7328																																																																																																																																																																																																																																																																																																																																																																																																																	
10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329																																																																																																																																																																																																																																																																																																																																																																																																																	
12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330																																																																																																																																																																																																																																																																																																																																																																																																																	
14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331																																																																																																																																																																																																																																																																																																																																																																																																																	
16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207		79107-7257	X	79107-7332																																																																																																																																																																																																																																																																																																																																																																																																																	
18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333																																																																																																																																																																																																																																																																																																																																																																																																																	
20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334																																																																																																																																																																																																																																																																																																																																																																																																																	
22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335																																																																																																																																																																																																																																																																																																																																																																																																																	
24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336																																																																																																																																																																																																																																																																																																																																																																																																																	
26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337																																																																																																																																																																																																																																																																																																																																																																																																																	
28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338																																																																																																																																																																																																																																																																																																																																																																																																																	
30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339																																																																																																																																																																																																																																																																																																																																																																																																																	
32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340																																																																																																																																																																																																																																																																																																																																																																																																																	
34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341																																																																																																																																																																																																																																																																																																																																																																																																																	
36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342																																																																																																																																																																																																																																																																																																																																																																																																																	
38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343																																																																																																																																																																																																																																																																																																																																																																																																																	
40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344																																																																																																																																																																																																																																																																																																																																																																																																																	
42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345																																																																																																																																																																																																																																																																																																																																																																																																																	
44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346																																																																																																																																																																																																																																																																																																																																																																																																																	
46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347																																																																																																																																																																																																																																																																																																																																																																																																																	
48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348																																																																																																																																																																																																																																																																																																																																																																																																																	
50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349																																																																																																																																																																																																																																																																																																																																																																																																																	
D															D																																																																																																																																																																																																																																																																																																																																																																																																																
C															C																																																																																																																																																																																																																																																																																																																																																																																																																
B	"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.														B																																																																																																																																																																																																																																																																																																																																																																																																																
A	<table><tr><td rowspan="5">CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLOIAO 2005/09/09 CHKD:80KOK 2005/09/09 APPR:PTLIM 2005/09/10</td><td rowspan="5">DESCRIPTION REV</td><td rowspan="5">F2</td><td rowspan="5">QUALITY SYMBOLS ▽=0 ▽=0</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES</td><td>mm</td><td>INCH</td><td>DRAWN BY AAB</td><td>DATE 1989/05/15</td><td rowspan="4">TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H MOLEX INCORPORATED</td></tr><tr><td>3 PLACES</td><td>mm</td><td>INCH</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>2 PLACES</td><td>mm</td><td>INCH</td><td>MJM</td><td>1989/05/15</td></tr><tr><td>1 PLACE</td><td>mm</td><td>INCH</td><td>APPROVED BY WAZ</td><td>DATE 1989/05/15</td></tr><tr><td colspan="4">ANGULAR ±1/2°</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">MATERIAL NO. SEE TABLE</td><td colspan="2">DOCUMENT NO. SDA-79107-****</td><td>SHEET NO. 3 OF 4</td></tr><tr><td colspan="11">SIZE A3</td><td colspan="3">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>														CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLOIAO 2005/09/09 CHKD:80KOK 2005/09/09 APPR:PTLIM 2005/09/10	DESCRIPTION REV	F2	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	4 PLACES	mm	INCH	DRAWN BY AAB	DATE 1989/05/15	TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H MOLEX INCORPORATED	3 PLACES	mm	INCH	CHECKED BY	DATE	2 PLACES	mm	INCH	MJM	1989/05/15	1 PLACE	mm	INCH	APPROVED BY WAZ	DATE 1989/05/15	ANGULAR ±1/2°				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-79107-****		SHEET NO. 3 OF 4	SIZE A3											THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			A																																																																																																																																																																																																																																																																																																																																																						
CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLOIAO 2005/09/09 CHKD:80KOK 2005/09/09 APPR:PTLIM 2005/09/10	DESCRIPTION REV	F2	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																																																																																																																																																																																																																																																																																				
				4 PLACES	mm	INCH	DRAWN BY AAB	DATE 1989/05/15	TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H MOLEX INCORPORATED																																																																																																																																																																																																																																																																																																																																																																																																																						
					3 PLACES	mm	INCH	CHECKED BY		DATE																																																																																																																																																																																																																																																																																																																																																																																																																					
					2 PLACES	mm	INCH	MJM		1989/05/15																																																																																																																																																																																																																																																																																																																																																																																																																					
					1 PLACE	mm	INCH	APPROVED BY WAZ		DATE 1989/05/15																																																																																																																																																																																																																																																																																																																																																																																																																					
ANGULAR ±1/2°				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-79107-****		SHEET NO. 3 OF 4																																																																																																																																																																																																																																																																																																																																																																																																																					
SIZE A3											THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																																																																																																																																																																																																				
	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																																					

MOLDED VOID OPTION ASSEMBLIES WITHOUT PEGS

	ASSEMBLY		VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"	P.C. TAIL DIM. "C"	PLATING OPTION
CKT. SIZE	ITEM NO.		ROW	CKT. NO.(s)					
24		79107-5001			2	(24.19)	(22.00)	(3.00)	TIN/LEAD
			ROW B	6					
10		79107-5002			2	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5003			2	(26.19)	(24.00)	(3.00)	
			ROW B	5					
24		79107-5101			5	(24.19)	(22.00)	(3.00)	TIN
			ROW B	6					
10		79107-5102			5	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5103			5	(26.19)	(24.00)	(3.00)	
			ROW B	5					

"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.

NOTES

1. TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.
2. VOIDS CANNOT BE PRESENT IN BOTH ROWS ON A CONNECTOR.

CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLOI/AO CHKD:BO/KOK APPR:PTL/IM	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H MOLEX INCORPORATED	SHEET NO. 4 OF 4		
						DRAWN BY AAB		DATE 1989/05/15						
						CHECKED BY MJM		DATE 1989/05/15						
						APPROVED BY WAZ		DATE 1989/05/15						
						MATERIAL NO.		DOCUMENT NO.						
F2				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SDA-79107-****						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														