




REV. 3
DCO 102710

COIL: @ 25°C
 RESISTANCE 75 OHMS ±10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 6.5 VDC
 MUST RELEASE .9 VDC


ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 50 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 15 MS MAX.
 OPERATE BOUNCE 5 MS MAX.
 RELEASE BOUNCE 5 MS MAX.

CUST. OPL
 CUST. NO. M5757/23-008 REV.

"07" RELAY

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: 10 AMPS 28 VDC
 5 AMPS 115 VAC/400 Hz RESISTIVE
 50,000 OPERATIONS

DR. R.B. 7/29/91 CK. TIG 8-17-01

CII Technologies
 advanced control electronic solutions

B07D634BB2-0118