

Indoor Break Glass Call Points



- Indoor surface mounting call points available as 470Ω or 680Ω versions
- Unique 'Plug & Play' installation concept
- Anti-tamper facility
- Enhanced aesthetics
- Fully approved to the latest standards, including EN54-11 and LPCB 166b/39 & 166b/40
- Backward compatibility
- Additional transparent hinged covers available for extra protection, ideal for schools etc
- Operating Temperature: -40 to +55°C
- Voltage: 24V DC
- Dimensions (WxHxD): 89 x 93 x 58.5mm

416661.416656

| Description              |  | Order Code | Price Each |
|--------------------------|--|------------|------------|
| Call Point 470Ω          |  | 100-4630   |            |
| Call Point 680Ω          |  | 100-4631   |            |
| Accessories              |  |            |            |
| Hinged Cover             |  | 100-4632   |            |
| Hinged Cover Seals (Pk5) |  | 100-4634   |            |
| Spare Glass (Pk10)       |  | 890-1970   |            |
| Spare Keys (Pk10)        |  | 100-4635   |            |