


Models 72919 2mm SAFETY Sheathed Patch Cords



Features

- 2mm Male to male straight fixed safety patch cord mates with 2mm jacks.

Materials

- Wire Insulation: PVC
- Plug Body: Nickel plated Brass
- Plug Insulation: Polypropylene
- Plug Tip Insulation: Polysulfone

Ordering Information

Model: 72919-Length-Color

Available lengths: 20 inches (-20) or 39 inches (-39)

Available colors: Black (-0) or red (-2)

Specifications

Max Current	10A
Max Voltage	33 Vrms / 70 Vdc
Temperature	-20° C + 80° C
Max Resistance	0.02Ω

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 International: 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm 0.02''$ (.51 mm), .xxx = $\pm 0.005''$ (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.