

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130103-0066](#)
Status: **Active**
Description: Watertite® Wet Location Incandescent Hand Lamp, 100W with TEFLON® Globe, Cord Type 16/2 SOOW, 15.24m (50.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374
UL E59049

General

Product Family Portable Lighting
Series [130103](#)
NEMA Configuration NEMA 1-15
NEMA Rating NEMA 4X
Outlet None
Product Literature Order No 987650-8053
Product Name Watertite®
Type Hand Lamps
UPC 78678861335
Woodhead Yes

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 127.00mm (5.000")
Duty Wet Location
Guard Included No
Guard Type N/A
Height 254.00mm (10.000")
Length N/A
Material - Globe PTFE
Material - Guard N/A
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/2 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120V AC

Material Info

Old Part Number 1225



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130103Series](#)