




P.C. Mounting

POS.1	POS.2
	
ON	ON
2-3	2-1
	

Switch Function



- Contact resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation resistance: 1,000MΩ min.
- Dielectric strength: 1,000 V RMS@sea level
- Rating: 1A / 250VAC; 3A / 120VAC or 28VDC

- Mechanical life: 50,000 make-and-break cycles
- Operating temperature: -30°C to 85°C

- RoHS Compliant by Exemption

- Manual soldering: use soldering iron of 30W, controlled at 350°C approx. 5 seconds while applying solder
- Wave soldering: recommended soldering temp.: 260±5°C Duration of solder immersion: 5±1 seconds (PCB is 1.6mm in thickness)

Mountain Switch

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2AS3T1717-EVX](#)