




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4203-003.
TUSONIX RoHS COMPLIANT PART NUMBER: 4203-003 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED COPPER. RoHS PART #: SILVER PLATED COPPER.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

MIN. CAP. (pF)	WORKING VOLTAGE (VVdc)		CURRENT IDC	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
1500	350	200	10A	10 G Ω	700	5	45	70	70

X-2015 Rev-0	REVISION RECORD			TOLERANCES unless otherwise specified	Title		
	Original Release	0	2898		BUSHING STYLE EMI FILTER		
	RDN TO COMP FMT, ADDED METRIC. S.M. 05-22-02	1	20020522-6-04				
	ADDED NOTES, IR & DWV. S.M. 11-14-05	2	20051026-5-04				
				2 PLC. DECIMAL ±	Drawn S.M. 05-22-02		
				3 PLC. DECIMAL ± .031 [0.79]	Scale 3 X		
				ANGLES ±	Approved J.Mc. 05-22-02		
				TUSONIX TUCSON, ARIZONA	A 4203-003		