




DETAIL Y

- MATERIAL:**
- HOUSING-DSM STANYL TE250F6 (NYLON-46)
HEAT DEFLECTION TEMP.290°
BLACK COLOR, UL94V-0
 - CONTACTS-0.35mm THICK PHOS-BRONZE
PLATED WITH HARD GOLD AND
GOLD FLASH IN SOLDER AREA.
 - SHIELD-0.25mm THICK COPPER ALLOY,
PLATED WITH NICKEL.
- CAVITY CONFIRMS TO FCC RULES AND REGULATIONS
PART 68,SUBPART F.



**PCB LAYOUT
Ref.**

Ordering Information

AJT65B	8	8	1	X
Type	Positions	Contacts	Ports	Plating 1 = 6u" 3 = 30u"

Tolerance unless otherwise specified mm
.0 ± 0.25
.00 ± 0.13
.000 ± 0.05

METZ CONNECT	P/N: AJT65B881X
Desc.: Side entry, shielded, thru hole modular jack	
Date: 9-09-09 Dimensions in mm	Drawn By: Donna Mears Verified By: Mike Balekdjian

● = Pin 1