

FLKM 50-PA-AB/1756/IN/EXTC

Order No.: 2302748

The illustration shows the version FLKM 50-PA-AB/1756/IN/EXTC



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2302748>

VARIOFACE front adapters, for Allen Bradley ControlLogix and Honeywell PlantScape, input card IB 32. The front adapters are pushed into the high 1756-TBE hoods (not supplied as standard).

Commercial data

GTIN (EAN)	4017918910471
sales group	I603
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.066 KG
Catalog page information	Page 190 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
08/15/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Channels which can be connected	32

Connection type, plug connector	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of plug connectors	1
No. of positions, plug connector	50
Number of positions	50
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Max. permissible current	1 A (per path)
Pollution degree	2
Surge voltage category	II
Supported controller	ALLEN-BRADLEY ControlLogix
Supported I/O card	1756-IB32
Supported controller	HONEYWELL PlantScape
Supported I/O card	TC-IDD 321

Certificates / Approvals




Certification

CUL, UL

Diagrams/Drawings

Circuit diagram



Connection scheme: FLKM 50-PA-AB/1756/IN/EXTC

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;